

Cable - CAB-TE MR36F/OE/24/S/ 3M - 2909732

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Migration cable for Bailey NET90/Infi90 to modern control platforms. Open-end cable for universal configurations, 36 conductors, 3.0 m

Your advantages

- ✓ Individual wire marking: 1, 2, 3, 4, etc.
- ✓ Individual wires fitted with ferrules
- ✓ Screw connection: 2 UNC 4-40 screws
- ✓ Open end at one end
- ✓ D-SUB socket or pin strip at one end
- ✓ 1:1 connection

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 055626 682570
GTIN	4055626682570

Technical data

General

Nominal voltage U_N	125 V AC
	125 V DC
Max. current carrying capacity per path	1 A
Length of cable	3 m
Single wire, cross section	0.25 mm ²
Single wire, cross section [AWG]	24
External diameter	10.5 mm
Shielding	yes
	Overall foil and braid shield

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Cable - CAB-TE MR36F/OE/24/S/ 3M - 2909732

Technical data

Color code

Connector 1 = connector 2 (optional) = wire color	MR36F (1) = black
	MR36F (2) = white
	MR36F (3) = red
	MR36F (4) = green
	MR36F (5) = orange
	MR36F (6) = blue
	MR36F (7) = white-black
	MR36F (8) = red-black
	MR36F (9) = green-black
	MR36F (10) = orange-black
	MR36F (11) = blue-black
	MR36F (12) = black-white
	MR36F (13) = red-white
	MR36F (14) = green-white
	MR36F (15) = blue-white
	MR36F (16) = black-red
	MR36F (17) = white-red
	MR36F (18) = orange-red
	MR36F (19) = blue-red
	MR36F (20) = red-green
	MR36F (21) = orange-green
	MR36F (22) = black-white-red
	MR36F (23) = white-black-red
	MR36F (24) = red-black-white
	MR36F (25) = green-black-white
	MR36F (26) = orange-black-white
	MR36F (27) = blue-black-white
	MR36F (28) = black-red-green
	MR36F (29) = white-red-green
	MR36F (30) = red-black-green
	MR36F (31) = green-black-orange
	MR36F (32) = orange-black-green
	MR36F (33) = blue-white-orange
	MR36F (34) = black-white-orange
	MR36F (35) = white-red-orange
	MR36F (36) = orange-white-blue

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>