

LED T 4.5 superbright, green, 24 V**1.90.690.332/0000****Electrical characteristics of LED**

Max. current, I_F	13 mA
LED wavelength typ.	630
Forward voltage typ. U_F at I_F	24
LED breakdown voltage U_R bei I_F	24
Light intensity	700

Other specifications

Socket	T 4.5
Color	green
Ambient temp. operating min.	-30 °C
Ambient temp. operating max.	+65 °C
ROHS compliant	yes
REACH compliant	yes