



Powering Business Worldwide

TRIPP LITE
SERIES

1U Rack-Mount Power Strip, 120V, 15A, 5-15P, 12 Right-Angle 5-15R Outlets (6 Front-Facing, 6 Rear-Facing), 15 ft. (4.57 m) Cord

MODEL NUMBER: RS-1215-RA



Delivers 120V power to rack-mount equipment in your network closet or server room.

Features

12-Outlet Power Strip for Your Rack Equipment

This 120V power strip is a versatile all-metal cabinet with 12 NEMA 5-15R outlets — six in front and six in back. The outlets are widely spaced to accommodate bulky transformers without blocking any outlets. Unfiltered electrical pass-through makes the RS-1215-RA ideal for distributing alternate waveform UPS or generator power in your data center or network closet's rack enclosure. The outlets are oriented at a right angle with the ground pin at the bottom.

Features Safety Standards and Versatile Installation Options

A lighted power switch with snap-in switch guard confirms on/off status at a glance and helps prevent accidental shutdowns. A 15A circuit breaker protects connected equipment. Detachable mounting brackets allow installation on a wall, under a counter or in 1U of space in an EIA-standard 19-inch rack. The 15-foot (4.6-meter) power cord with NEMA 5-15P plug connects to a compatible AC outlet.

Highlights

- 12 NEMA 5-15R outlets are spaced apart to accommodate bulky transformers
- Lighted on/off switch with plastic cover is protected against accidental turn-off
- 15 ft. cord with NEMA 5-15P plug is long enough to reach distant AC outlet
- Versatile installation on wall, under counter or in 1U of rack space

Package Includes

- RS-1215-RA 1U Rack-Mount Power Strip
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332099402
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15



Powering Business Worldwide

TRIPP LITE
SERIES

Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(12) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(9) Yes
Outlet Orientation	6 front-facing / 6 rear-facing, all with ground pin oriented to the bottom (when viewed in 1U rackmount configuration)
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
PHYSICAL	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Form Factors Supported	1U rackmount, wall-mount and undercounter installation supported
Housing Color	Black
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	Distance between Front outlets = 2.03 in.; Distance between Rear outlets = 2.79 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	9.30 x 2.25 x 20.30
Shipping Dimensions (hwd / cm)	23.62 x 5.72 x 51.56
Shipping Weight (lbs.)	5.32
Shipping Weight (kg)	2.41
Unit Dimensions (hwd / in.)	1.750 x 19.000 x 4.000
Unit Dimensions (hwd / cm)	4.445 x 44.45 x 11.4
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
Mounting Details	Includes Rackmount flanges
ENVIRONMENTAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Operating Temperature Range	32° to 113°F (0° to 45°C)
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	Yes
Grounding	Back panel nut and bolt grounding lug
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.