

## product details

---

### Product Searches

- [7/16](#)
- [1.0/2.3](#)
- [1.6/5.6](#)
- [AFI](#)
- [AMC](#)
- [BNC / RP-BNC](#)
- [C](#)
- [FAKRA SMB](#)
- [FME](#)
- [HN](#)
- [MCX](#)
- [Mini-UHF](#)
- [Mini 75 ? SMB](#)
- [MMCX](#)
- [Precision \(APC\)](#)
- [QMA](#)
- [SC](#)
- [SlimLine BNC](#)
- [SMA / RP-SMA](#)
- [SMB](#)
- [SMC](#)
- [SMP](#)
- [SSMB](#)
- [TNC / RP-TNC](#)
- [Triax](#)
- [True 75 ? BNC](#)
- [Twin BNC](#)
- [Twinax](#)
- [Type F](#)
- [Type G](#)
- [Type N](#)
- [UHF](#)
- [Reverse Polarity](#)



*Please note: Images are for reference only*

<b>Amphenol Part Number:</b>	031-5637
<b>Description:</b>	Low Profile
<b>Product Series:</b>	<a href="#">BNC</a>
<b>Product Type:</b>	<a href="#">Connectors</a> » <a href="#">Printed Circuit Board</a>
<b>Body Plating:</b>	<a href="#">Nickel</a>
<b>Connector Body Style:</b>	<a href="#">Right Angle</a>
<b>Contact Plating:</b>	<a href="#">Gold</a>
<b>Gender:</b>	<a href="#">Jack</a>
<b>Grade:</b>	<a href="#">Industrial</a>
<b>Impedance:</b>	<a href="#">50 Ohm</a>
<b>Terminal Type:</b>	<a href="#">Blunt Post</a>
<b>RoHS Certificate:</b>	<a href="#">Yes</a>
<b>More Information:</b>	<a href="#">Customer Drawing</a> <a href="#">Distributor Inventory</a>

- 
- [Adapters](#)
  - [Cable Assemblies](#)
  - [Tools](#)
  - [Accessories](#)

---

[Product Search](#)

---

[Inventory Search](#)