



+ TERMINALS & SPLICES

QUICK DISCONNECTS



✓ Active

TE CONNECTIVITY (TE)

MINI FASTON 110 REC 24-20 AWG PTPBR

FASTON | 110

151614-1

TE Internal Number: 151614-1

EU RoHS Compliant

EU ELV Compliant

Terminal Type Receptacle

Wire Size (AWG) 24 – 20

Wire Size (mm²) .2 – .6

Mating Tab Width 2.8 mm [.11 in]

Mating Tab Thickness .51 mm [.02 in]

[!\[\]\(bff896c19919791b89ab521f039b410a_img.jpg\) **PRODUCT DRAWING**](#)
English

[!\[\]\(23a2e9ddc7bb0ef55393d38b772a848d_img.jpg\) **3D PDF**](#)

DOCUMENTATION

Product Drawings

.110 SRS MINI. FASTON RECEPTACLE SPECIAL SHORT

PDF (TIFF AVAILABLE)

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Agency Approvals

Agency Approval Document

SERIES 6.35 FASTONS

PDF

English

UL Report

Quick Connect Connectors FASTON Series 110, 187, 205, 250

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminates To Wire & Cable

FASTON Yes

Insulated Wire Support No

Disconnect Type Quick Connect

Insulated No

Wire/Cable Type Discrete Wire

Wire Stop No

Wire/Cable Composition Stranded

Configuration Features

Connection Capacity Single

Body Features

Plating Material Tin

Contact Features

Terminal Type Receptacle

Terminal Orientation Straight

Barrel Type Open

Crimp Type F-Crimp

Mechanical Attachment

Mating Retention Type Dimple

Dimensions

Wire Size (AWG) 24 – 20

Wire Size (mm²) .2 – .6

Mating Tab Width 2.8 mm [.11 in]

Mating Tab Thickness .51 mm [.02 in]

Receptacle Stock Thickness .25 mm [.01 in]

Overall Length 7.75 mm [.305 in]

Industry Standards

CSA Certified Yes

UL Rating Listed

Packaging Features

Packaging Method Reel

Packaging Quantity 20000

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
