



CONNECTORS

STANDARD RECTANGULAR CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

1.5 MINI CT LATTICE REC KEY A

AMP MINI-CT | AMP Mini CT Lattice

2-292246-2

TE Internal Number: 2-292246-2

EU RoHS Compliant

EU ELV Compliant

Product Type Connector

UL Flammability Rating UL 94V-0

Number of Positions 26

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

RECEPTACLE ASSEMBLY FOR AMP 1.5 PITCH MINI CT HYBRID LATTICE CONNECTOR

PDF

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

3D PDF

PDF

English

Product Specifications

Product Specification

AMP Mini Hybrid Lattice Connector, 1.5mm Pitch Lead Free Version

PDF

Japanese

Product Environmental Compliance

TE Material Declaration

MD_2-292246-2_0617201659_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Connector

Configuration Features

Number of Positions 26

Number of Power Positions 4

Keying A

Number of Signal Positions 10 + 12

Body Features

Color Gray

Lattice Contact Mating Area Plating Material Gold

Housing Features

Housing Color Gray

Housing Material Thermoplastic

Dimensions

Width (mm) 25.4

Height (mm) 25.9

Length (mm) 53.7

Industry Standards

UL Flammability Rating UL 94V-0

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
