

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

? Connector Type = Standard
? Wire Range = 0.12 - 0.40 ² [26-22] mm
[AWG]
? Insulation Outer Diameter = .46 -
1.22 mm
? Weather Resistant
? Air Core PIC Cable Insulation
Material, Foam Filled PIC Cable
Insulation Material

[View all Features](#) | [Find Similar](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

[CONN, W/R, PURPLE, PICABOND](#) (PDF, English)

? None Available

? None Available

[PICABOND Regular & Weather Resistand Regular Connectors](#)
(PDF, English)

? None Available

? None Available

? Product Line Information

? Tooling

List all Documents

(Please use the Product Drawing for all design activity)

? Connector Type = Standard

? Color Code = Purple

? Wire Range (mm [AWG]) = 0.12 - 0.40 ² [26 - 22]

? Insulation Outer Diameter (mm [in]) = 0.46 - 1.22 [0.018 - 0.048]

? Weather Resistant = Yes

? Cable Insulation Material = Air Core PIC, Foam Filled PIC

3 Contact Mating Area Plating Material = Tin

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Packaging Method = Loose Piece

? Brand = AMP