



Specification:

Materials:

Shell: Tin Plated Steel
 Insulator: PBT Thermo Plastic, Black Color, 30% Glass Filled
 Self-Extinguishing, UL94V-0 rated
 Contact Material: Pin: Brass, Socket: Phosphor Bronze
 Contact Plating: Gold over Nickel

Electrical:

Current Rating: 5.0 Amps
 Dielectric Strength: 1000 VAC min.
 Insulation Resistance: 5000m ohm min
 Operating Temperature Range: -55°C~ +125°C

Dimensions

# of Pins	A	B	C
9	16.33	24.99	30.81
15	24.66	33.32	39.14
25	38.38	47.04	53.04
37	54.84	63.50	69.32
	2.159	2.500	2.729

Features and Options:

- Available in 9, 15, 25, and 37 positions
- Male and Female Versions
- Available with hardware options such as threaded inserts and hex stands-offs, board locks and grounding straps
- Gold plated contacts
- Tin plated shell

Description	
Name :	A-DXXXA-KG-TXXX3
	D-Sub Connector Right Angle



THIS DRAWING IS UNPUBLISHED

© Copyright 2005 by Assmann Electronic Components All International Rights Reserved

This drawing is a controlled document for Assmann Electronics, Inc. It is subject to change and the controlling engineering organization should be contacted for the latest revision.