

4





PART NO.	CABLE LENGTH +5%/-0	
31186-1810	10 FT	
31186-1820	20 FT	
31186-1830	30 FT	
31186-1850	50 FT	
31186-1875	75 FT	
31186-18100	100 FT	
31186-18150	150 FT	

NOTES (UNLESS OTHERWISE INDICATED)

- 1. MAT'L: MS310618-1S INLINE PLUG, 37048-003 CABLE, **BLACK POLYURETHANE OVERMOLD**
- OPERATING TEMP -40 TO +80°C 2.

4

- 3. STANDARD BEI (SENSATA)PINOUT/WIRE COLOR
- LENGTHS OVER 50 FT DO NOT HAVE MOLDED BACKSHELL 4.

TWISTED PAIR	COLOR	
PAIR 1	YELLOW	
	W/YELLOW	
PAIR 2	BLUE	
	W/BLUE	
PAIR 3	ORANGE	
	W/ORANGE	
PAIR 4	RED	
	BLACK	

UNCON	ITROLLED	COPY	
FIRST ISSUE DATE: 04/04/19	SENSATA TECHNOLOGIES PROPR CONFIDENTIAL. NEITHER THIS PRI INFORMATION CONTAINED HEREON AGAINST THE INTERESTS OF SENSATA OR AGAINST THE INTERESTS OF ANY C COMPANIES OR WHOLLY OWNED INTERPRET DIMENSIONING AND T PER ASME Y14.5-2009. UNLESS SPECIFIED DIMENSIONS A INCHES [MILLIMETERS] AND ARE I NOMINAL SEE PRODUCT SPECIFIC MORE DETAILS.		
DRAWN: DRC			
APPROVED; MFB			
DATE: 04/04/19 ECN: DATE:			
MATERIAL:	DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION	
2 DEVICE:			

А

D

С

В