


[Home](#) > [Search Tools](#) > [Part Number](#)

Part Number Search

 You Searched For:

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.

ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.

Our Descriptive Part Number: DA24658


Our Global Manufacturing Part Number: 024658-0000

<input type="checkbox"/>	CONSULT FACTORY	RoHS compliant =	material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2002/95/EC
	CONSULT FACTORY	RoHS compatible =	Compatible with lead free soldering process

Export Compliance

<input type="checkbox"/>	Country of Compliance	United States
	Export Compliance Notes	Commercial Shipments "C" Controlled by the US Department of Commerce.

Product Datasheet

Thumbnail Image	
Product Group	D Subminiature Accessories
Where Sold	Asia Pacific, Americas, Europe
D Sub Accessory type	Metal Endbell
Application Type	Commercial, Military/High Reliability
Shell Size	DA
D Sub Accessory Style	Deep Straight Clamp
Endbell Material	Low Carbon Steel
Endbell Finish	Yellow chromate over cadmium
Hardware Material	Steel
Cable Entry	7,93 (.312)
Dimension A	38,89 (1.531) ±0,38 (.015)
Dimension B	12,484 (.4915) ±0,572 (.0225)
Dimension C	33,32 (1.312) ±0,13 (.005)
Dimension D	14,68 (.578) max.
Dimension E	18,11 (.713) ±0,38 (.015)
Dimension F	7,93 (.312) ±0,38 (.015)
Dimension G	19,05 (.750) ±0,38 (.015)
Dimension H	31,75 (1.250) max.
Note	Kit consists of 1 shell, 2 cable clamps, 2 screws, 2 hex nuts.
Footnote	Dimension are shown in mm (inch). Dimensions subject to change.
For more information	Please Contact Cannon Sales Department.
MIL-SPEC Part Number	M85049-48-1-2