

J82-16001 K-1 Series Business Keyboards



**Reliable Business Keyboard
with Compact Durable Package**

Not recommended for new designs, we suggest our JK-0800EU.

Key Features

- Comfortable Key Action
- Space-efficient Compact Keyboard
- Abrasion-proof Writing on Keycaps

Main Part Numbers

- J82-16001LUNEU-0**
Light grey color, USB interface
- J82-16001LUNEU-2**
Black color, USB interface
- J82-16001LPNEU-0**
Light grey color, PS/2 interface
- J82-16001LPNEU-2**
Black, PS/2 interface

Technical Data

Interface

USB or PS/2 Interface

Current Input

typ. 40 mA

Number of Keys

104 position US Key Layout

Cable Length

approx. 1.80 m

Weight

approx. 650 g (keyboard)
approx. 780 g (with packaging)

Dimensions

approx. 460 x 165 x 32 mm (keyboard)
approx. 485 x 190 x 36 mm (packaging)

Packaging Units

10 keyboards per master carton
20 master cartons per pallet

Keyswitch Lifetime

>10 million operations

Storage Temperature

-20 °C to 60 °C

Operating Temperature

0 °C to 50 °C

Agency Approvals

FCC, CE, C-Tck cURus, GHOST-R,
Microsoft Windows™ XP

Delivery Volume

Keyboard, Printed

Warranty

2 years

Contact

Call, fax or visit our website for more information.

Last Update 3/4/2014

ZF Electronic Systems Pleasant Prairie, LLC

11200 88th Avenue
Pleasant Prairie, WI 53158

Phone: 262.942.6500
Web: www.cherrycorp.com

E-Mail: keyboardsupport@zf.com
Fax: 262.942.6566

CHERRY 