



What can we help you find?

[Products](#) [Industries](#) [Resources](#) [About TE](#) [My Account](#) [Innovation](#) [Support Center](#)

MINISMDC014F-2 Product Details

[Share](#)[Print](#)[Email](#)**Active**

PolySwitch Resettable Devices

MINISMDC014F-2

MINISMDC014F-2 (RF1334-000)

TE Internal Number: RF1334-000

Product Highlights [View All](#)

- Surface Mount Application
- Family Name = miniSMD
- Vmax = 60 V
- Imax = 10 A
- IH (Room Temperature) = .14 A

[Pricing & Availability](#)[Request Sample](#)[Add to My Part List](#)[Buy Product through Distributor](#)[Documents](#)[Features](#)[Compliance](#)**Please Note:**

Use the Product Drawing for all design activity

Product Type Features

Family Name	miniSMD
CSA File Number	CA78165

Electrical Characteristics

Vmax (V)	60
Imax (A)	10
IH (Room Temperature) (A)	0.14
IT (Room Temperature) (A)	0.28
Rmin (Ω)	1.50
R1 Max [Post Trip] (Ω)	6.00

Termination Features

Construction	Surface Mount
--------------	---------------

Configuration Features

Form Factor (inches)	1812
Form Factor (mm)	4532

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Reflow solder capable to 245°C, Reflow solder capable to 260°C
RoHS/ELV Compliance History	Always was RoHS compliant
TUV Certificate No.	R72111045
UL File Number	E74889

Environmental

Operating Temperature (Max.) (°C)	85
-----------------------------------	----

Operation/Application

Application	Surface Mount
-------------	---------------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product
you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms of Use of TE.com](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)
- [Terms & Conditions of Sale](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

