

CATALOG

- [Cross Reference](#)
- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Circuit Protection Devices

↳ PolySwitch Resettable Devices

Raychem MINISMDC200F-2  Active

**Directive 2002/95/EC
Compliant**

RoHS Compliant

(Corporate P/N: A86932-000)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ➤ General Info ➤ Sales Info 	<ul style="list-style-type: none"> ➤ Pricing & Availability 	<ul style="list-style-type: none"> ➤ Tooling

Searchable Features:

Brand:	Raychem
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Reflow solder capable to 245°C, Reflow solder capable to 260°C
Application:	Surface Mount
Family Name:	miniSMD
Construction:	Surface Mount
IH (Room Temperature) (Amps.):	2
IT (Room Temperature) (Amps.):	4.00
Operating Temperature (Max.) (°C):	85
Vmax Operating (V):	8
Rmin (•):	0.02

Other Properties:

RoHS/ELV Compliance History:	Always was RoHS compliant
Tripped Power Dissipation (Typical) (W):	1.00
UL Listed:	091199-E74889
CSA File No.:	1031175 (CA 78165-1)
TUV Certificate No.:	R72041438
Packaging Method:	Tape & Reel

<u>R1 Max [Post Trip] (°):</u>	0.07
<u>UL Rated Current (Amps.):</u>	100
<u>Form Factor (inches):</u>	1812
<u>Form Factor (mm):</u>	4532

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]

▪