



AUTOMATION & CONTROL

MOTION

SWITCHES & POSITION SENSORS

ELECTRICAL PROTECTION

COCKPIT CONTROLS

| WWW.CROUZET.COM

| 2

PRODUCTS OVERVIEW

WWW.CROUZET.COM

PRODUCTS OVERVIEW

ABOUT CROUZET

Since 1921, Crouzet has been committed to designing, manufacturing and supplying efficient components for automated systems to serve a wide range of application in the Aerospace & Defense market; in many Industrial equipment markets, with a specific focus on applications such as Access control, Railway, Nuclear and Industrial valves.

Crouzet's product lines include Automation and Control devices, Motion products, Switches and Position Sensors, Cockpit Controls and Electrical Protection products. Crouzet has a heritage of close collaboration with customers in the development of adapted products to fully customized solutions.

Driven by innovation and customer satisfaction, our teams are focused on delivering the right products and services for the right application, always meeting, and often exceeding customers' expectations.

Crouzet is your trusted partner of choice to face the challenges of today and tomorrow.

Crouzet is a company of InnoVista Sensors™.



InnoVista Sensors™ is a worldwide industrial specialist of sensors, controllers and actuators for automated systems.

Through its brand Crouzet, InnoVista Sensors™ offers a wide range of reliable, efficient and customizable components dedicated to the Aerospace & Defense, Transportation and Industrial markets and segments.

Thanks to the recognized expertise of its teams and a strong innovation policy, InnoVista Sensors™ brings performance enhancing solutions to its customers worldwide.

InnoVista Sensors™: your trusted partner of choice to face industrial challenges of today and tomorrow.

www.innovistasensors.com

Designs & Manufactures







Controls

Actuators

For







Transportation



Industr

CONTENT

	PAGES
Excellence Overview	04
Adaptation Wheel	05
Automation & Control	06-07
Motion	08-09
Switches & Position Sensors	10-11
Electrical Protection	12
Cockpit Controls	13
Note	15

WWW.CROUZET.COM

PRODUCTS OVERVIEW

EXCELLENCE OVERVIEW

OUR MARKETS







Aerospace & Defense

Railway

Automotive







Access Control

Nuclear

Other Industrial Applications

OUR QUALITY SYSTEM

Quality Management

- ISO 9001
- ISO 14001
- ISO 18001

Automotive

•ISO/TS 16949

Nuclear

- EDF certification
- RCC-E

- AS/EN 9100
- NADCAP
- EASA approved (Part 21G & Part 145)

Hazardous Locations

• ISO/IEC80079-34 (ATEX/IECEx)

Aerospace















































ADAPTATION WHEEL

Crouzet has developed extensive expertise in adapting its products based on standard ranges, including the necessary project planning skills when it involves a new program.

SPECIAL PRODUCT

From the very start of a project, Crouzet's team experts work closely with your teams to develop the specifications.

All our design, industrialization and approval expertise go into developing solutions. We focus our design, manufacturing and qualification expertise on developing a new product designed to meet your requirements.

STANDARD PRODUCT

A full range of microswitches, limit switches, manually operated switches, motors and geared motors, including AC synchronous, brush and brushless DC and stepper motors. are immediately available so that you can design your system as quickly as possible.



Complete coordination between your project teams and our specialists, these adapted products have exactly the right levels of performance and functionality you need for your applications.

All projects are different, so we adapt the performance and functionality of each product to your requirements, ensuring the success of your most complex applications.



All our standard products can have additional factory-mounted auxiliaries or accessories, including connectors, leads, special terminals, fixings, levers, software etc. Seamless integration into your equipment means you benefit from simpler logistics and optimum installation reliability.





















WWW.CROUZET.COM | PRODUCTS OVERVIEW | WWW.CROUZET.COM PRODUCTS OVERVIEW

AUTOMATION & CONTROL

Our experience in physical and electrical values has resulted in an offer which includes timers, monitoring relays, counters, microcontrollers and PLCs.

As a pioneer in the simplification of programming, we offer the easiestto-use and most adaptable solution for specialized needs.



MARKETS & APPLICATIONS

- > Building Equipment
- > Industrial OEMs
- > Access Control

TELECONTROLLER em4 Alert



- > Connect your equipment to the 3G GPRS network wherever you are
- › Automatic alerts via text message and e-mail minimize the downtime of machines and systems
- > Simple monitoring and Control via text message
- > Receive data reports via text message or datalogs via email or FTP in .CSV (Excel) file
- > Adapt your application along the way of its lifecycle thanks to the remote application program update feature via FTP



NANO-PLC m4 Ethernet/Local



- > Up to 46 I/Os Base 16 DI (4 HighSpeed/ 12 AI), 8 DO + 2 Solid State Relays
- Analog Inputs 4-20 mA, 0-10 VDC and 0-VDC 12 bits
- > Ethernet Modbus TCP/IP (Client/Server) and Modbus RTU RS485 via interface (Master/Slave)
- > Event management & datalog via mail or FTP server
- > PLC performance with the shape and ease of use of



LOGIC CONTROLLER

Millenium EVO





- > Wireless programming & control with bluetooth Interface and Crouzet Virtual Display
- > Ethernet Modbus TCP/IP (Client/Server) and Modbus RTU Network via interface (Slave)
- > Event and Datalog Managment via mail/FTP server or Locally
- > Up to 1000 programing blocks with intuitive Crouzet Soft to go from simple to complex applications



> Highly visible blue LCD with 4 lines of 18 characters and configurable backlighting

Millenium 3

- > Allow the use of the entire library of specific functions blocs of the software workshop
- > Extended temperature range (-20 °C → +70 °C)
- > Parameter setting: possibility to choose the adjustable parameters on the front panel



SOFTWARES

Visual programming and a wide choice of pre-programmed function blocks for the most intuitive and easy-to-use software, even for new users, and it is free.

rouzet	Soft

Crouzet Virtual Display








COMPLEMENTARIES PRODUCTS: EM4, MILLENIUM EVO, MILLENIUM 3



- Touch screen 4.3 / 7 / 9.7 pouces
- > Digital extensions and analog extensions
- > T° probes
- > Light sensors
- > Starter kits
- > Powers supplies





		COUNTERS			
		SyrLine		Chronos 2	
	Sometimes of the state of the s	SCHOOL IN THE STREET OF THE ST	Scientify Tourism		150 160 200000
Max counting	0.5 s → 240 H	0.5 s → 240 H	0.055 s → 9999 H	0.5 s → 100 H	0.001 s → 999.999 H
Outputs	1x16 A or 2x8 A	1x8 A or 2x8 A	1x5 A or 2x10 A	1x8 A or 2x8 A	
Dimensions	17.5 mm DIN rail mount	35 mm Removable	48 x 48 mm panel mount	17.5 & 22.5 mm DIN rail mount	24x48 mm / 48x48 mm
Supply	12 → 240 V≂	12 → 240 V≂	24 → 240 V≂	12 → 240 V≂	$10 \rightarrow 30 \text{ V} = /24 \text{ V} \sim$ $90 \rightarrow 260 \text{ V} \sim$
	INFO				

RELATED PRODUCTS: PNEUMATICS COMPONENTS

- > Human/Machine Interface Components
- > Position Detectors
- > Pressure Switches
- > Electro-Pneumatic Valves
- > Pneumatic Logic Components
- > Industrial Vacuum Components











- > Water and Waste Treatment
- > Renewable Energy

 | WWW.CROUZET.COM
 | 8
 | PRODUCTS OVERVIEW

 | WWW.CROUZET.COM
 | 9
 | PRODUCTS OVERVIEW

MOTION

We provide a
complete offer of
direct drives, geared
motors and motion
control solutions for
applications where
performance is key.
Our customized
solutions meet
most customers'
demanding
specifications where
security, reliability and
precision are crucial.

POSITION, SPEED AND TORQUE REGULATION

	MOTORS							
	Industrial Brush	DCmind Brush	DCmind Brushless	Stepper	Synchronous			
			THE CONTRACTOR OF THE CONTRACT			THE WAY		
	Ø 32 / Ø 42 Ø 63	Ø 42 / Ø 63	SQ57 SQ75	Ø 35 / 51 Ø 57 / 65	Ø 35 Ø 57			
Nominal Power (W)	0,9 → 95	15 → 104	66 → 600	0.5 → 5	0.3 → 3	0.2 → 0.4		
Voltage	12 / 24 / 48 VDC	12 → 120 VDC	9 → 75 VDC	3 → 64 VDC	24 → 24 50 →	40 VAC 60 Hz		
Nominal Speed (rpm)	3000 → 3700	3000	3000	1500	250 → 600	600 / 720		
Nominal Torque (mNm)	2.2 → 270	50 → 290	125 → 1900	15 → 300	10 → 110	2.5 → 8		
Noise Level (dBA)	55	35	45 / 50	35	30	45		
Service Life (hrs)	Up to 5 000	Up to 5 000	20 000	20 000	20 000	10(Mr*) on/off		
Gearboxes				+ †	<u>+</u>	t		
Connection	(C)							
More information								
	Connect	cor Cable		ead	Termi	inal		
	Worm	Plane	etary P	arallel Shaft	Sile	ent		

	CONTROL ELECTRONICS						
		External					
	TNi21	SMi21	SMi22	BDE 30 / BDE 40			
Compatible models	SC	157	SQ75	SQ57			
Speed Torque	•	•	•	•			
Position (c/t)		4096	4096				
Programming		DCmind Soft & DCmind Soft + CANopen	DCmind Soft + CANopen	PWM or 0 → 10 V			
Communication Bus		CANOPEA Option	CANOPEA Standard				
Voltage	10 → 36 V===	9 → 75 V===	9 → 75 V===	10 → 36 V			
Maximum Current (A)	17	17	75	14			



GEARBOXES







	Spur gear	Planetary	Worm		
	10 models	7 models	2 models		
Torque (Nm)	0.5 → 6	0.8 → 120	10 → 20		
Power (W)	0.2 → 50	8 → 600	25 → 600		
Service life (Mr*)	1 → 10	50	50		
Ratios	4 → 4500	4 → 308	5 → 100		
Options	Shafts: stainless steel, pulleys, pinions, special bearings etc.				

INFO +





Medical

> Valves and Pumps

> Energy Distribution

> Industrial Automation

> Access Control

Agriculture and Forestry







DCMIND SOFT (SMI21) & DCMIND SOFT+CANOPEN (SMI21 & SMI22) FOR DCMIND BRUSHLESS

- > Precise configuration of the position, speed and torque
- > The most user-friendly software on the market
- > Two programming modes: application & expert
- Application programs: dosing, valves, machinery, conveyor belt, access control
- * Free software on our website (motors.crouzet.com) or can be supplied on a USB stick in the «starter kit».



^{*} Million revolutions

WWW.CROUZET.COM 10 PRODUCTS OVERVIEW WWW.CROUZET.COM 11 PRODUCTS OVERVIEW


SWITCHES & POSITION SENSORS


As specialist in snap action technologies our offer includes microswitches. limit switches and manually operated switches which are adaptable in terms of connectors, lever or body size.

High quality and reliability products are crucial in harsh environments with severe constraints

DETECTION & SENSING

MICROSWITCHES									
	S	ub-Subminia	ture			ubminiature A		liniature & Special	
								7500	
Series	V5S 8320	83228 83229	V5D 83194 83141	V4/V4D 83170 8327	V4S 8318	83132 83133 83134	V3/V3D 83161/160 8326	V3S/V3DS 83169 8329	PBX 8324
Max Rating @250 Vac (A)	4 A	5 A	5 A	12 A	10 A	6 A	25 A	10 A	10 A
Low level version	I(mA)	I(mA)	I(mA)	I(mA)	I(mA)	I(mA)	I(mA)	I(mA)	I(mA)
Sealing level	IP67 IP69				IP67 IP69			IP67 IP69	IP65 IP67
Double break						Za			Zb
Operating temperature	-40 °C +90 °C	-55 °C +140 °C	-55 °C +150 °C	-40 °C +150 °C	-40 °C +125 °C	-40 °C +150 °C	-60 °C +150 °C	-40 °C +105 °C	-50 °C +85 °C
Environment									
Approval	c PN us (CC) EHI	c SN us EAC	c PN us Œ EHI		ERIC	c PN us (CC) EAC		c PN us (CC) EHI	c PN us Œ EAC
More information									

















CUSTOMIZED SOLUTIONS

- > Dedicated application
- > Customer specific product
- > Innovation & industrialization



MANUALLY OPERATED SWITCHES

- > Pushbuttons, Momentary and/or Maintained, up to 4 poles
- > Toggles, Maintained and/or Momentary, up to 4 poles
- Multiway, Momentary
- > Rockers, Momentary and Maintained
- > Triggers, Momentary



 | WWW.CROUZET.COM
 | 12
 | PRODUCTS OVERVIEW

 | WWW.CROUZET.COM
 | 13
 | PRODUCTS OVERVIEW

ELECTRICAL PROTECTION

LIGHT, SIMPLE, SAFE

Specialist in Electrical
Protection Devices,
our products are
involved in advanced
electrical equipment
onboard aircrafts and
helicopters.
Our expertise in
innovative technolo-

gies and our

compliance with

has given us the

reputation of top

space industry.

player in the aero-

industry standards

ELECTROMECHANICS, MECHATRONICS, ELECTRONICS Solid State Power Circuit Breaker Panel Circuit Breaker > Intrinsic fail safe > Illuminated front panel > Single channel > Multiple terminal options > Qualification > CAN 2.0 bus documentation for FAA > Signal contacts Key features or EASA certification > Adaptable to customers' requirements Power supply 28 VDC & 115 VAC 28 VDC & 115 VAC 28V DC & 115 VAC Mechanical life $1 M \rightarrow 7 M FH$ 20 000 FH 20 000 FH Quick installation Pushfit Pushfit & PWB NA Weight < 20 g 1000 - 4000 g $170 \rightarrow 250 \text{ g}$ Operating temperature -55 → +125 °C -55 → +85 °C -55 → +70 °C More information







MARKETS & APPLICATIONS

- > Commercial Aircrafts
- > Business Jets
- Military Aircrafts
- > Helicopters
- > Ground Vehicles
- > Landing gear
- > Electrical Distribution
- > Flight Controls


COCKPIT CONTROLS


With technicallyadvanced custom
grips, control wheels,
and buttons, our offer
is suitable for major
programs worldwide.
The large range of
pushbuttons and
accessories makes it
possible to provide
solutions for all
necessary requirements.

THE DETAILS THAT MAKE THE DIFFERENCE

	FLIGHT CONTROLS							
	Pushbutton	Multiway	Pilot Grip	Control Wheel				
	Social States	Nose VP						
Key features	> 1, 2, 3, 4 pole > Sealed versions > More than 200 electrical combinations	> Tactile effect > Silver & gold terminals > Different hat shape and color	> Ergonomy and functions access > Aluminium castings or injected in advanced plastic composite > Highest level of finishing	Comfort and aesthetics Best in class quality Leather finishing				
Operating force	8N → 16N	3N → 6N	90 daN	150 daN				
Mechanical life	300 000	500 000	35 000 FH	35 000 FH				
Water proofness	DO 260 cat W	DO 260 cat W	DO 260 cat W	DO 260 cat W				
Weight	$3.6 \text{ g} \rightarrow 7.7 \text{ g}$	7.3 g → 15.7g	420 g → 780 g	960 g → 1 250 g				
Operating temperature	-55 °C → +85 °C	-55 °C → +85 °C	-55 °C → +85 °C	-55 °C → +85 °C				
More information								

NOTE







AMERICAS

EUROPE / MIDDLE EAST / AFRICA

ASIA / PACIFIC

CANADA

MEXICO

USA

+1 (855) 929-5465

Tel.: +1 (855) 929-5465 americas.custserv@crouzet.com

FRANCE

BELGIUM

Tel.: +1 (855) 929-5465 americas.custserv@crouzet.com

Tel.: +33 (0) 475 802 101 Fax: +33 (0) 475 828 900

Tel.: +32 (0) 2 620 06 05

Fax: +32 (0) 2 461 00 23 klantenservice@crouzet.com

Tel.: +49 (0) 2103/9385930

COUNTRIES NOT LISTED

+1 (855) 929-5465 americas.custserv@crouzet.com

americas.custserv@crouzet.com

relationclient@crouzet.com

GERMANY / AUSTRIA

Fax: +49 (0) 2103/980-222 kundenservice@crouzet.com

ITALY

Tel.: +39 (02) 38 594 099 Fax: +39 (02) 82 952 104 assistenzaclienti@crouzet.com

SPAIN / PORTUGAL

Tel.: +34 (91) 215 80 95 Fax: +34 (93) 2 20 02 05 atencionalcliente@crouzet.com

SWITZERLAND

Tel.: +41 (0) 225 67 57 90 Fax: +41 (0) 565 88 02 75 kundenservice@crouzet.com

THE NETHERLANDS

Tel.: +31 (0) 20-654 52 20 klantenservice@crouzet.com

UNITED KINGDOM

Tel.: +44 (0) 2076 600 025 customer.relation@crouzet.com

COUNTRIES NOT LISTED

Fax: +33 (0) 475 828 900 customer.relation@crouzet.com

CHINA

Tel.: +86 (21) 8025 7166 Fax: +86 (21) 6107 1771 china@crouzet.com

INDIA

Tel.: +91 (80) 6762 4501/500 india@crouzet.com

SOUTH KOREA

Tel.: +82 (2) 2679 8312 Fax: +82 (2) 2679 9888 korea@crouzet.com

EAST ASIA PACIFIC

Fax: +86 (21) 6107 1771 eap@crouzet.com

Warning:

The product information contained in this catalogue is given purely as information and does not constitute a representation, warranty or any form of contractual commitment. Crouzet Automatismes SAS and its subsidiaries reserve the right to modify their products without notice. It is imperative that we should be consulted over any particular use or application of our products and it is the responsibility of the buyer to establish, particularly through all the appropriate tests, that the product is suitable for the use or application. Under no circumstances will our warranty apply, nor shall we be held responsible for any application (such as any modification, addition, deletion, use in conjunction with other electrical or electronic components, circuits or assemblies, or any other unsuitable material or substance) which has not been expressly agreed by us prior to the sale of our products.

