

Part Number : 5530183200F



General Description

Series	553
Description	CBI 3MM BI-LEVEL B-G
Package Options	Bulk Packaging
Lamp Type	Bi-Level Housing
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25°)

Derating	0.25 (mA/degC)
Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics

Peak Wave Length	585
Luminous Intensity Min	7.4
Luminous Intensity Typical	10
Forward Voltage Typical	2.1
Forward Voltage Max	2.8
Test Current mA	20mA



This is a
RoHS Compliant Product
[To learn more click here](#)