

Electroswitch Power Switches

Highest quality for the most demanding applications

Ratings to 20 Amp — 1 HP 100,000 Cycle Operation Sealing Options Available

High Electrical Load Harsh Environments

Longest Life

Electroswitch Electronic Products • 2010 Yonkers Road • Raleigh, North Carolina 27604 Phone: 888-768-2797 • Fax: 800-909-9171 • sales@electro-nc.com WWW.ELECTRO-NC.COM

7000 and 9000 Series Toggle

Electrical Rating: 15A - 125 VAC 10A - 250 VAC Life Cycles: 100,000 Electrical 100,000 Mechanical Operating Temp: -10°C to +65°C



FL ()

F) (R

Sealing: bushing seal tested per IP67 standards to withstand submersion in water to a depth of 1 meter for 30 minutes

7100 and 9100 Series Toggle

Electrical Rating: 6A - 125 VAC

3A - 250 VAC

Life Cycles: 25,000 Electrical Optional 75,000 with silver rocker

50,000 Mechanical

Optional 100,000 with silver rocker

Operating Temp: -10°C to +65°C Sealing: bushing seal tested per IP67 standards to withstand submersion in water to a depth of 1 meter for 30 minutes

7300 and 9300 Series Toggle

Electrical Rating: 20A - 125 VAC 10A - 250 VAC 1 HP, 125-250 VAC

Life Cycles: 100,000 Electrical 100,000 Mechanical

Operating Temp: -10°C to +65°C

Sealing: bushing seal tested per IP67 standards to withstand submersion in water to a depth of 1 meter for 30 minutes

7000 Series Pushbutton

Electrical Rating: 15A - 125 VAC 10A - 250 VAC Life Cycles: 100,000 Electrical 100,000 Mechanical

Operating Temp: -10°C to +65°C

7100 Series Pushbutton

Electrical Rating: 6A - 125 VAC 3A - 250 VAC Life Cycles: 25,000 Electrical Optional 75,000 with higher torque spring 50,000 Mechanical Optional 100,000 with higher torque spring Operating Temp: -10°C to +65°C



A) (()

Flier EEP–PT RevA ©Copyright Electroswitch 2012

7200 and 9200 Series Toggle

Electrical Rating: 20A - 125 VAC

10A - 250 VAC

3/4 HP, 125-250 VAC Life Cycles: 100,000 Electrical

100,000 Mechanical

Operating Temp: -10°C to +65°C

Sealing: bushing seal tested per IP67 standards to withstand submersion in water to a depth of 1 meter for 30 minutes

7600 and 9600 Series Toggle

Electrical Rating: 5A - 30 VDC Life Cycles: 25,000 Electrical

Optional 75,000 with silver rocker

- 50,000 Mechanical
- Optional 100,000 with silver rocker

Operating Temp: -10°C to +65°C

Sealing: bushing seal tested per IP67 standards to withstand submersion in water to a depth of 1 meter for 30 minutes

6600 Series Toggle

Electrical Rating: 10A - 125 VAC 12A - 125 VAC 1/3 HP, 125 VAC Life Cycles: 25,000 Electrical

50.000 Mechanical

Operating Temp: -10°C to +65°C



6611 Series Pushbutton Electrical Rating: 10A - 125 VAC 12A - 125 VAC

1/3 HP. 125 VAC Life Cycles: 25,000 Electrical 50.000 Mechanical Operating Temp: -10°C to +65°C



Our Toggle Boots offer additional protection in the most severe environmental conditions, providing full protection against exposure to harsh elements such as water, oil, sand, dust, dirt, humidity, moisture, precipitation and other contaminants.



Electroswitch Electronic Products 2010 Yonkers Road • Raleigh, North Carolina 27604 Phone: 888-768-2797 • Fax: 800-909-9171 • sales@electro-nc.com WWW.ELECTRO-NC.COM

