

Datasheet

Item No. 96.151.1053.1

Female connector RST20i5C B1 M01 SW

Device connectors, standard M25, RST20i5, 5 pole, female, crimp connection, 250/400V, 20A, color of coding: black, color of nut: black



Item No.	96.151.1053.1
EAN	4015573933347
order unit	100 Piece(s)

Approvals



Technical data

General

Rated current	20 A
Rated voltage	400 V
Pollution degree	3
Mechanical coding	Yes
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Black
Connection cross section solid	4 mm ²
Connection cross section stranded	4 mm ²
Terminations per pole	1

Model

Model	Bus
Number of poles	5
Connection type	Crimp
Connecting thread metric	M25
Angle of plug	Straight
Degree of protection (IP)	IP66/IP68
Built-in component	Snap-in/screw-in

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn

Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	44 mm
Width	35 mm
Height	35 mm

Drawings

