

YAEV4C-RS

YAEV4GRS

YAEV4GRS : 1/4 RIGHTANGLE,4,TPCU



ACTIVE

RoHS compatible

BURNDY® PRODUCTS

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Specifications

Download document

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Strip length (Wire)	1/2 in.		
Stud Hole (Size)	1/4 in.		
Tongue Angle	90°		
Tongue Width (in)	0.53 in.		
Wire Shroud	No		
Insulation Diameter (Max)	0.374 in.		
Physical			
Conductor Size	4 AWG		
Conductor Type	Commercial/Military Stranded Copper		
Insulation Type	Nylon		
Color Code	Yellow		
Conductor Size (Range)	4 AWG		
Approvals / Certifications			
Military Listed	MIL-T-7928		
UL Listed	No		
CSA Certified	No		
Other Features			
Tongue Type	Ring		
UPC	78181003951		
Keyword	smltermHC		