

« Accessories

Fluke i400 AC Current Clamp

Fluke i400 AC current clamps extend the use of digital multimeters. Get a single range 400 A AC clamp in a compact shape. Buy Online Now.

Buy Now

Manuals

★★★★★ 5.0 (2)

Write a review



Overview

Features

Reviews

Specs

Models

Accessories

Resources

Product Registration

Model (1)

Model Name

Description

Fluke i400

Fluke i400 AC Current Clamp

Top Related Products



Fluke 1587/ET Advanced Electrical Troubleshooting Kit »



Fluke 1587/MDT Advanced Motor and Drive Troubleshooting Kit »



Fluke 77 IV Digital Multimeter »

★★★★★ 5.0 (9)



Fluke 83V Average Responding Industrial Multimeter »

Overview

Features

Reviews

Specs

Models

Accessories

Resources

 Product Registration

Specifications

Nominal current range	400 A
Continuous current range	1 A - 400 A
Maximum non-destructive current	1000 A
Lowest measurable current	1 A
Basic accuracy	2% + 0.06 A (45-400 Hz) (% reading + floorspec)

Useable frequency 5 Hz - 20 kHz

Output level(s) 1 mA/A

Safety Specifications

Safety	CAT IV 600 V, CAT III, 1000 V
Maximum voltage	1000 V AC rms from earth to ground, in compliance with EN61010

Mechanical and General Specifications

Warranty	1 year
Maximum conductor diameter	32 mm (1.25 in)
Maximum conductor size (busbar)	750 MCM
Output cable length	1.5 m (59 in)
Shrouded banana plugs	Yes

Top Related Products



Fluke 1587/ET Advanced
Electrical
Troubleshooting Kit »



Fluke 1587/MDT
Advanced Motor and
Drive Troubleshooting
Kit »



Fluke 77 IV Digital
Multimeter »

★★★★★ 5.0 (9)



Fluke 83V Average
Responding Industrial
Multimeter »