HBL7485V -- Twist-Lock Valise Plug



3P3W, 15A 125/250V, ML-3P, Black Nylon Body

Product Specifications

Product Type	
	Twist-Lock
	Davicas

Body Holding Screw

Link to PDF Catalog

Withstand

Steel zinc plated

Click here for Catalog

	Twist-Lock Devices
Product Item	Plug
Wiring Scheme	3-Pole, 3-Wire Non-Grounding
Amperage	15A
Voltage	125/250V AC
NEMA Configuration	ML-3P
Item Style	Valise
Device Color	Black
Cord Dia.	.300"430" (7.6-10.9)
Blade Holder Material	Black Nylon
Housing Material	Black nylon
Cord Clamp Material	Nylon
Blade Material	Brass
Terminal Clamp Material	Cold rolled steel-nickel-plated
Cord Clamp Screw Material	Steel zinc plated

Material	Steel zinc plated
Ratings	Molded In or Stamped On
Catalog No	Permanently ink marked on product
Dielectric Voltage	2,000 minimum

Current Interrupting	Certified for current interrupting at full rated current
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75

factor of .75.
Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62,

Cord Accommodation	CSA C22.2 No. 49.
Terminal Accommodation	15A #14 AWG

Terminal Accommodation	
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6

Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)

Moisture Resistance	IP20
Listings	III

Listings	UL
UPC Number	783585237435

UPC Number	183383231433
Weight in LBs	0.1

Weight in LBs	0.1
Link to Drawing Library	Click here for Library



NEMA Configuration

