

HBLC40163FL -- Commercial Cord Reel



Reel with Fluorescent Hand Lamp and Inline Receptacle, White

Product Specifications

Reel Type	 Commercial Cord Reels
Commercial Reel Type	Reel with Fluorescent Hand Lamp and Inline Receptacle, White
Cable Length	40' (12.20)
Voltage	125V AC
Amperage	10A
Listings and Certifications	UL 355
Operation	Dry, Indoor, Non-Hazardous Locations
Classification	Commercial/Industrial
Fluorescent Lamp	10A/1200W Max with In-Line Receptacle; 13 Watt without Receptacle
Description	Commercial Cord Reels are designed for the less demanding requirements of commercial and light industrial environments. The commercial reels feature steel construction and have a 125V rating with SJT type cord. These reels are UL listed and provide power
Notes:	Reels supplied with 2 ft. power supply cord and molded on straight blade 15A plug.
UPC Number	78358552486
Weight in LBs	9.2
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

