



[Previous Page](#)

[Printer Friendly](#)

[Version](#)

Product: **PIEZO SOUNDER WITH BUILT-IN
CIRCUIT**

Description: **ROHS COMPLIANT UPON REQUEST**

Part Number: **BPS6055L-12-C**

SPECIFICATIONS:

RATED VOLTAGE:	12 VDC
OPERATING VOLTAGE:	6 ~ 12 VDC
MAX CURRENT:	350 mA
SOUND OUTPUT LEVEL:	115dB @ 1M
TERMINAL TYPE:	2 LEADWIRES
RESONANT FREQUENCY:	2500-3000 Hz
OPERATING TEMPERATURE:	-20 TO +70 °C
TONE MODE:	SIREN
FRAME DIAMETER:	60 x 55 mm
FRAME DEPTH:	85.0 mm
MOUNTING DIMENSIONS:	35.0 mm

DIMENSIONS:

