



[Previous Page](#)

[Printer Friendly](#)

[Version](#)

Product: **PIEZO SOUNDER WITH BUILT-IN
CIRCUIT**

Description: **ROHS COMPLIANT**

Part Number: **BPS8432L-12-C**

SPECIFICATIONS:

RATED VOLTAGE:	12 VDC
OPERATING VOLTAGE:	6 ~ 15 VDC
MAX CURRENT:	85 mA
SOUND OUTPUT LEVEL:	105dB @ 1M
TERMINAL TYPE:	2 LEADWIRES
RESONANT FREQUENCY:	2500-2800 Hz
OPERATING TEMPERATURE:	-20 TO +70 °C
TONE MODE:	CONTINUOUS
FRAME DIAMETER:	84 x 55 mm
FRAME DEPTH:	32.0 mm
MOUNTING DIMENSIONS:	97.5 mm

