



[Previous Page](#)

[Printer Friendly](#)

[Version](#)

Product: **PIEZO SOUNDER WITH BUILT-IN
CIRCUIT**

Description: **ROHS COMPLIANT**

Part Number: **BPS9234S-24-C**

SPECIFICATIONS:

RATED VOLTAGE:	24 VDC
OPERATING VOLTAGE:	6 ~ 28 VDC
MAX CURRENT:	150 mA
SOUND OUTPUT LEVEL:	115dB @ 1M
TERMINAL TYPE:	SCREW
RESONANT FREQUENCY:	2800 Hz
OPERATING TEMPERATURE:	-20 TO +70 °C
TONE MODE:	CONT., SIREN or
FRAME DIAMETER:	92 x 92 mm
FRAME DEPTH:	34.0 mm
MOUNTING DIMENSIONS:	72.0 mm

DIMENSIONS:

