

Incandescent

Fluorescent

LED

Inverter

PRODUCT SEARCH



STOCK CHECK



Home > Incandescent > Bi-Pin Lamps

Incandescent | Bi-Pin Lamps

For Bi-Pin LEDs please click [Here](#).

Click on column headers below to sort the table. All headers to the left of comments are sortable.

Part Nbr	Size	Volts	Amps	MSCP	Life	Comments	Specs (pdf)	RFQ	Rerate
3149	T-1 3/4	5	n/a	0.15	5000	n/a	link	request	rerate
7001	T-1 3/4	24	n/a	0.5	2000	Buy Now	link	request	rerate
7022	T-1	5	n/a	n/a	10000	Buy Now	link	request	rerate
7114	T-3/4	5	n/a	n/a	100000	n/a	n/a	request	rerate
7118	T-3/4	5	0.115	0.15	40000	n/a	n/a	request	rerate
7263	T-1	5	n/a	n/a	16000	Buy Now	link	request	rerate
7265	T-1	5	n/a	0.15	5000	n/a	link	request	rerate
7268	T-1	5	0.125	0.22	5000	n/a	link	request	rerate
7327	T-1 3/4	28	n/a	0.34	4000	Buy Now	link	request	rerate
7328	T-1 3/4	6	0.2	0.6	1000	Buy Now	link	request	rerate
7330	T-1 3/4	14	n/a	0.5	2500	Buy Now	link	request	rerate
7344	T-1 3/4	10	0.014	n/a	50000	Buy Now	link	request	rerate
7349	T-1 3/4	6.3	0.2	0.55	5000	Buy Now	link	request	rerate
7361	T-1 3/4	5	n/a	n/a	100000	Buy Now	link	request	rerate
7362	T-1 3/4	5	0.115	0.15	40000	Buy Now	link	request	rerate
7367	T-1 3/4	10	n/a	n/a	30000	Buy Now	link	request	rerate
7368	T-1 3/4	6.3	0.15	0.45	3000	Buy Now	link	request	rerate
7370	T-1 3/4	18	n/a	0.15	10000	Buy Now	link	request	rerate
7371	T-1 3/4	12	n/a	0.12	10000	Buy Now	link	request	rerate
7373	T-1 3/4	14	0.1	0.5	50000	Buy Now	link	request	rerate
7373/BLA/39-10-4E	T-1-2	14	0.1	0.5	5000	7373 w/ 10-39 Filter	link	request	rerate
7374	T-1 3/4	28	n/a	0.2	50000	Buy Now	link	request	rerate
7375	T-1 3/4	3	n/a	n/a	10000	Buy Now	link	request	rerate
7376	T-1 3/4	28	n/a	0.65	5000	Buy Now	link	request	rerate
7377	T-1 3/4	6.3	n/a	0.023	1000	Buy Now	link	request	rerate
7380	T-1 3/4	6.3	0.04	0.03	20000	Buy Now	link	request	rerate
7381	T-1 3/4	6.3	0.2	0.4	50000	Buy Now	link	request	rerate
7382	T-1 3/4	14	n/a	0.3	50000	Buy Now	link	request	rerate
7387	T-1 3/4	28	n/a	0.3	7000	Buy Now	link	request	rerate
7632	T-1 1/4	28	n/a	0.32	1000	n/a	link	request	rerate
7680	T-1	5	n/a	n/a	100000	n/a	link	request	rerate
7683	T-1	5	n/a	n/a	40000	Buy Now	link	request	rerate
7683EBP	T-1	5	n/a	n/a	40000	n/a	link	request	rerate
7683SBP	T-1	5	n/a	n/a	40000	n/a	link	request	rerate
7714	T-1	5	n/a	n/a	25000	Buy Now	link	request	rerate
7715	T-1	5	0.115	0.15	40000	Buy Now	link	request	rerate
7715EBP	T-1	5	0.115	0.15	40000	n/a	link	request	rerate
7715SBP	T-1	5	0.115	0.15	40000	n/a	link	request	rerate
7732	T-1	2.5	0.1	0.1	10000	n/a	link	request	rerate
7838	T-1 3/4	2.7	n/a	n/a	6000	Buy Now	link	request	rerate
7839	T-1	28	0.024	0.15	16000	Buy Now	link	request	rerate
7839EBP	T-1	28	0.024	0.15	16000	n/a	link	request	rerate
7839SBP	T-1	28	0.024	0.15	16000	n/a	link	request	rerate
7876	T-1 3/4	28	n/a	0.34	25000	Buy Now	link	request	rerate
7945	T-1 3/4	6	n/a	n/a	10000	n/a	link	request	rerate
8095	T-1	10	0.027	0.1	10000	Buy Now	link	request	rerate
8097	T-1	12	n/a	0.15	16000	Buy Now	link	request	rerate
8097EBP	T-1	12	n/a	0.15	16000	n/a	link	request	rerate
8097SBP	T-1	12	n/a	0.15	16000	n/a	link	request	rerate
8098	T-1	14	n/a	0.15	16000	Buy Now	link	request	rerate
8098SBP	T-1	14	n/a	0.15	16000	n/a	link	request	rerate
8099	T-1	18	n/a	0.15	16000	Buy Now	link	request	rerate
8099EBP	T-1	18	n/a	0.15	16000	n/a	link	request	rerate
8099SBP	T-1	18	n/a	0.15	16000	n/a	link	request	rerate
CB44	T-1	12	n/a	n/a	10000	n/a	link	request	rerate
CB48SBP	T-1	14	n/a	0.15	16000	n/a	link	request	rerate
GB12417	G-4	12	0.417	n/a		n/a	n/a	request	rerate

If you cannot find what you are looking for, [contact us](#).

TOP ▲

Product Information

Bi-Pin

Bi Pin Incandescent Lamps, Dual rigid leads: The bi-pins are offered in various sizes and can be used with mating sockets or can be directly mounted onto a P.C. board. Different heights are available to accommodate low profile requirements or taller height requirements. Selected bases offer venting for outgassing during the solder process. Colored filters are available to fit all standard size bi-pins.

Case Study:

No Case Study for this family...