

Tool Online Catalog

Select a Category



GO

CRIMPERS

[Product Index](#) > [Strippers, Cutters, Crimpers](#) > [Crimpers](#) > 1005

Crimping/Cutting Tool — Non-Insulated/Insulated Connectors

- Accommodates wire from No. 10 to 22 AWG.
- Specially hardened wire cutter in nose.
- Tapered nose design for working in confined spaces.
- Crimping die marked for insulated and non-insulated solderless terminals and connectors.
- Plastic-dipped, cushioned handles for comfort.
- Hot-riveted joint for smooth action and no handle wobble.



Pictured: 1005

Cat. No.	Crimps	Handle Color	Overall Length	Weight (lbs.)
1005	10-22 AWG	red	9-3/4" (248)	.80

All dimensions are in inches and (millimeters) except where indicated.

[Download High-Resolution .jpg photo](#)

[Download High-Resolution .eps photo](#)



The downloadable files are compressed in .zip format to save on downloading times. Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

⚠ WARNINGS: Always wear approved eye protection.

⚠ WARNINGS: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).