



Select a Category

GO

MIDGET CURVED CHAIN-NOSE PLIERS

[Product Index](#) > [Pliers](#) > [Long-Nose Pliers](#) > [Midget Curved Chain-Nose Pliers](#) > D320-41/2C

Midget Curved Chain-Nose Pliers

- 60° bent nose for maximum work visibility in confined areas.
- Easily bends and forms fine wire.
- Polished inside jaws and radiused jaw edges prevent nicking wire.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



Buy Now!

Pictured: D320-41/2C

Cat. No.	Handle Color	Handle Finish	Jaw Length	Jaw Thickness	Jaw Width	Overall Length	Point Thickness	Weight (lbs.)
D320-41/2C	royal blue	plastic-dipped	1" (25)	1/4" (6)	13/32" (10)	4-3/4" (121)	1/16" (1.6)	.13

All dimensions are in inches and (millimeters) except where indicated.

Download High-Resolution .jpg photo

Download High-Resolution .eps photo



The downloadable files are compressed in .zip format to save on downloading times. Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

 **WARNINGS:** Always wear approved eye protection.

 **WARNINGS:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).