

Digital Multimeter, Auto-Ranging, 1000V



Cat. No. MM700

Product Features

- Automatic ranging true root mean square (TRMS) technology for increased accuracy
- Measures up to 1000V AC/DC voltage, 10A AC/DC current and 40M Ω resistance plus temperature, capacitance, frequency, duty-cycle, diodes and continuity
- CAT IV 600V Safety Rating
- Built to withstand a 6.6' (2m) drop and withstand daily wear and tear on the job site
- Low Impedance (LoZ) mode for identifying and eliminating ghost or stray voltages
- For use in basic and controlled electromagnetic environments such as residential, business and light-industrial locations
- Low battery indicator and easily accessible battery and fuse replacement compartment
- Includes carrying pouch, test leads, alligator clips, thermocouple with adapter and batteries

Buy Now

Find Retailer



Specs

Video

Downloads

Warnings

Accessories

Replacement Parts

Buy Now

Batteries:

2 x AAA

Depth:

2.1"

Drop Protection:

6.6 ft. (2 m)

Height:

7"

Included

Ingress Protection:

Accessories:

IP 42

Pouch, Test Leads, Thermocouple, Batteries, Alligator Clips

Safety Rating:

CAT IV 600V

Weight (oz.):

Width:

14.6 (414 grams)

3.54