

Security Doors

Our keylocked steel security doors allow front access to a select portion of rackmount equipment and are available in plexiglass, vented, and solid steel styles. Mount equipment which needs to be secured behind the solid door to keep unauthorized users from tampering. Keep equipment which needs to be client accessed in the open portion of the rack. Works as a full door on our RK/BRK series racks as well.

Solid Part #	Plexi Part#	Vented Part#	Racking Height
SSDR-8*	PSDR-8*	VSDR-8*	14" (8 space)
SSDR-12	PSDR-12	VSDR-12	21" (12 space)
SSDR-15	-	-	26-1/2" (15 space)
SSDR-16	PSDR-16	VSDR-16	28" (16 space)
SSDR-20	PSDR-20	VSDR-20	35" (20 space)
SSDR-21	-	-	36-3/4" (21 space)

*8 space doors include a single lock, larger sizes include two locks



Hinged Plexiglass Security Covers

Incorporating a steel frame and a keylocked 3/16" smoked-grey plexiglass door, our SEOL series locking security covers are offered in 2, 3, 4, and 8 space sizes. Each unit's depth of 1 1/2" easily clears controls on most equipment.

Part #	Racking Height
SECL-2	3-1/2" (2 space)
SECL-3	5-1/4" (3 space)
SECL-4	7" (4 space)
SECL-8	14" (8 space)





Perforated Security Covers

Eliminate the prospect of any tampering with these tough security covers. Offered in large or fine perforation styles (models S and SF respectively), each cover is 1" deep. Includes installed rubber edging that won't mar the equipment you're trying to protect. To enhance the level of security, use our security rack screws.



Туре	Part #	Descripton
allows unobstructed view of knob settings	S1	1 sp. (1-3/4") regular perf. pattern
	S2	2 sp. (3-1/2") regular perf. pattern
	S3	3 sp. (5-1/4") regular perf. pattern
	S4	4 sp. (7") regular perf. pattern
allows sight of LED's most secure	SF1	1 sp. (1-3/4") fne perf. pattern
	SF2	2 sp. (3-1/2") fine perf. pattern
	SF3	3 sp. (5-1/4") fine perf. pattern
	SF4	4 sp. (7") fine perf. pattern

A&E Spec. #96-035 Download or view PDF file

Plexiglass Security Covers

SL series security covers feature a permanent plexiglass window for easy equipment viewing. Secure and cost-effective - available in 1, 2, and 3 space sizes, 1" deep.

Racking Height
1-3/4" (1 space)
3-1/2" (2 space)
5-1/4" (3 space)

