



Positions	Dim. A	Dim. B	Mode Part #
2	2.54	5.66	37-602-0
3	5.08	8.20	37-603-0
4	7.62	10.74	37-604-0
5	10.16	13.28	37-605-0
6	12.70	15.82	37-606-0
8	17.78	20.90	37-608-0
9	20.32	23.44	37-609-0

Specifications:

Current Rating: 3A AC/DC
 Voltage Rating: 250V AC Max.
 Temperature Range: -25°C to 90°C
 Contact Resistance: Initial Value / 10 mΩ Max.
 Insulation Resistance: 5000 MΩ Min.
 Dielectric Withstanding: 1500V AC / Minute
 Applicable Wire: #22 - #30 AWG
 Insulator: UL 94V-0
 Insulator Color: White

Display Packages (37-602-5, 37-603-5, 37-604-4, 37-605-3, 37-606-3, 37-608-2 and 37-609-2) include 37-960-0 Contacts

(Number of Contacts = Number of Positions)

TITLE		SCALE
.100" WIRE CONNECTOR		NTS
DRAWING NO.	37-6XX	
		UNITS mm
FILE NAME	37-6XX.pdf	SHEET 1/1



Mode Electronics Part Number 'multi-parts'