

[Home](#) | [Find a Distributor](#) | [About Us](#) | [Contact](#) | [Products](#) | [New Products](#) | [Technical](#) | [Disty/Rep Login](#)

PART# / PRODUCT SEARCH

68-6030PS-1

GO >>

[Item Index](#)[Mode Catalog](#)[Lenline Part# Convert](#)[AC Adapters](#)[Audio Products](#)[Battery Holders](#)[Bottles and Dispensers](#)[Brushes](#)[Buzzers/Alarms](#)[CATV Products](#)[Circuit Breakers](#)[Coaxial Connectors](#)[Computer Accessories](#)[Connectors](#)[DC Power Products](#)[Earphones/Microphones](#)[Fans](#)[Fuseholders/Fuses](#)[Hardware](#)[IC Sockets](#)[Knobs](#)[LED Products](#)[Lamps/Pilot Lamps](#)[Miscellaneous Items](#)[Plastic Boxes](#)[Potentiometers/L-Pads](#)[Power Cords/Jacks/Bars](#)[RF Adapters](#)[Relays](#)[Rubber Feet/Grommets](#)[Speakers/Speaker Wire](#)[Switches](#)[Telephone Products](#)[Test Equipment](#)[Tools/Tool Cases](#)[Transformers](#)[Video Products](#)[Wiring Products](#)[Latent Fingerprint Brush](#)[Show drawing \(PDF\)](#)

SWITCHING POWER SUPPLY - REGULATED OUTPUT

These switching power supplies will accept input voltages of 90-240VAC 50/60Hz and will provide a constant output voltage (within approx. 10%) from no load to full rated current load. All are cULus approved as well as CE and other approvals. The desk top units come complete with power cords. The RoHS is 2011/65/EU.

Voltage 6VDC@3A**Type** center positive**68-6030PS-1** [Display Pkg](#)

These switching power supplies provide a regulated output voltage regardless of the current used.

[Home](#) | [About Us](#) | [Contact Us](#)

©2009 Mode Electronics Ltd.



