

- ALL MG PRODUCTS ▾
- + Dusters & Cold Sprays
 - + Cleaning Products for Electronics
 - + Protective Coatings
 - + Adhesives
 - + Greases and Lubricants
 - + Prototyping and Circuit Repair
 - + Solder and Solder Related Products
 - + RTV Silicones
 - + Epoxies
 - Specialty Products
 - 3D Printing
 - 3D Printer Filaments**
 - 3D Printing Accessories
 - 3D Printing Chemicals

Find the latest compliance letters and certificate. Learn more about FoodSafe, REACH & RoHS.

FoodSafe REACH RoHS

3D Printer Filaments – PLA NEW

PLA

[BUY NOW](#)

- Description** | Technical Data | MSDS | Usage Instructions

The optimal choice for use in homes, schools, and hobbyists. Based on corn, this product biodegrades. It gives off a mild non-offensive sweet smell when heated, making the product suitable for home use. It does not require a heated print bed, and it easily adheres to masking tapes. It is very hard, acetone resistant, and when properly utilized can achieve faster print speeds and lower layer heights than [ABS](#).

Features & Benefits

- PLA
- 1.75mm and 3.0mm diameters
- Vivid colors
- Low Diameter variance
- High Purity USA made PLA pellets
- Colors as unique as Light Skin, Gold, Silver, Glow In The Dark, etc.
- 0.25 KG spools
- 0.50 KG spools
- 1.00 KG spools



Available Colors

1 2 Next >

1 2 Next >



RED [Download Full Size](#)

Part Selection Tool

Quick Find: [Clear Filters](#)

Material	Diameter (mm)	Color	Weight	Part Number
PLA	1.75	Translucent	0.25 kg spool	PLA17TL25
PLA	1.75	White	0.25 kg spool	PLA17WH25
PLA	1.75	Black	0.25 kg spool	PLA17BK25
PLA	1.75	Red	0.25 kg spool	PLA17RE25
PLA	1.75	Yellow	0.25 kg spool	PLA17YE25
PLA	1.75	Green	0.25 kg spool	PLA17GR25
PLA	1.75	Blue	0.25 kg spool	PLA17BL25
PLA	1.75	Orange	0.25 kg spool	PLA17OR25
PLA	1.75	Purple	0.25 kg spool	PLA17PU25
PLA	1.75	Grey	0.25 kg spool	PLA17GY25
PLA	1.75	Brown	0.25 kg spool	PLA17BR25
PLA	1.75	Gold	0.25 kg spool	PLA17GO25
PLA	1.75	Silver	0.25 kg spool	PLA17SI25
PLA	1.75	Green (Glow in the Dark)	0.25 kg spool	PLA17GD25
PLA	1.75	Light Skin	0.25 kg spool	PLA17SK25
PLA	1.75	Navy	0.25 kg spool	PLA17NA25
PLA	1.75	Lime	0.25 kg spool	PLA17LI25
PLA	3	Translucent	0.25 kg spool	PLA30TL25
PLA	3	White	0.25 kg spool	PLA30WH25
PLA	3	Black	0.25 kg spool	PLA30BK25
PLA	3	Red	0.25 kg spool	PLA30RE25
PLA	3	Yellow	0.25 kg spool	PLA30YE25
PLA	3	Green	0.25 kg spool	PLA30GR25
PLA	3	Blue	0.25 kg spool	PLA30BL25
PLA	3	Orange	0.25 kg spool	PLA30OR25
PLA	3	Purple	0.25 kg spool	PLA30PU25
PLA	3	Grey	0.25 kg spool	PLA30GY25
PLA	3	Pink	0.25 kg spool	PLA30PI25
PLA	3	Brown	0.25 kg spool	PLA30BR25
PLA	3	Gold	0.25 kg spool	PLA30GO25
PLA	3	Silver	0.25 kg spool	PLA30SI25

Material	Diameter (mm)	Color	Weight	Part Number
All	All	All	All	
PLA	3	Green (Glow in the Dark)	0.25 kg spool	PLA30GD25
PLA	3	Light Skin	0.25 kg spool	PLA30SK25
PLA	3	Navy	0.25 kg spool	PLA30NA25
PLA	3	Lime	0.25 kg spool	PLA30LI25
PLA	1.75	Translucent	0.5 kg spool	PLA17TL5
PLA	1.75	White	0.5 kg spool	PLA17WH5
PLA	1.75	Black	0.5 kg spool	PLA17BK5
PLA	1.75	Red	0.5 kg spool	PLA17RE5
PLA	1.75	Yellow	0.5 kg spool	PLA17YE5
PLA	1.75	Green	0.5 kg spool	PLA17GR5
PLA	1.75	Blue	0.5 kg spool	PLA17BL5
PLA	1.75	Orange	0.5 kg spool	PLA17OR5
PLA	1.75	Purple	0.5 kg spool	PLA17PU5
PLA	1.75	Grey	0.5 kg spool	PLA17GY5
PLA	1.75	Pink	0.5 kg spool	PLA17PI5
PLA	1.75	Brown	0.5 kg spool	PLA17BR5
PLA	1.75	Gold	0.5 kg spool	PLA17GO5
PLA	1.75	Silver	0.5 kg spool	PLA17SI5
PLA	1.75	Green (Glow in the Dark)	0.5 kg spool	PLA17GD5
PLA	1.75	Light Skin	0.5 kg spool	PLA17SK5
PLA	1.75	Navy	0.5 kg spool	PLA17NA5
PLA	1.75	Lime	0.5 kg spool	PLA17LI5
PLA	3	Translucent	0.5 kg spool	PLA30TL5
PLA	3	White	0.5 kg spool	PLA30WH5
PLA	3	Black	0.5 kg spool	PLA30BK5
PLA	3	Red	0.5 kg spool	PLA30RE5
PLA	3	Yellow	0.5 kg spool	PLA30YE5
PLA	3	Green	0.5 kg spool	PLA30GR5
PLA	3	Blue	0.5 kg spool	PLA30BL5
PLA	3	Orange	0.5 kg spool	PLA30OR5
PLA	3	Purple	0.5 kg spool	PLA30PU5
PLA	3	Grey	0.5 kg spool	PLA30GY5
PLA	3	Pink	0.5 kg spool	PLA30PI5
PLA	3	Brown	0.5 kg spool	PLA30BR5
PLA	3	Gold	0.5 kg spool	PLA30GO5
PLA	3	Silver	0.5 kg spool	PLA30SI5
PLA	3	Green (Glow in the Dark)	0.5 kg spool	PLA30GD5
PLA	3	Light Skin	0.5 kg spool	PLA30SK5
PLA	3	Navy	0.5 kg spool	PLA30NA5
PLA	3	Lime	0.5 kg spool	PLA30LI5
PLA	1.75	Lime	0.5 kg spool	PLA30LI5
PLA	1.75	Translucent	1.0 kg spool	PLA17TL1
PLA	1.75	White	1.0 kg spool	PLA17WH1
PLA	1.75	Black	1.0 kg spool	PLA17BK1
PLA	1.75	Red	1.0 kg spool	PLA17RE1
PLA	1.75	Blue	1.0 kg spool	PLA17BL1
PLA	3	Translucent	1.0 kg spool	PLA30TL1
PLA	3	White	1.0 kg spool	PLA30WH1
PLA	3	Black	1.0 kg spool	PLA30BK1
PLA	3	Red	1.0 kg spool	PLA30RE1
PLA	3	Blue	1.0 kg spool	PLA30BL1

