

PRODUCT CATALOG

> [Switches and Indicators](#) > [Toggle Switches](#) > [Multi-Pole Toggle Switches](#)

Multi-Pole Toggle Switches

McGill full-size double pole, 3 pole and 4 pole toggle switches are available in a variety of circuit arrangements and different terminal types to meet your electrical requirements. Metallic toggle and threaded bushing ensure extended service life. All switches are UL Recognized and CSA Certified.

Specifications

- **6 Amp, Double Pole**
6A, 125V AC;
3A, 250V AC;
1/4 HP, 125-250V AC; 50/60 Hz
Suitable for 6A, 12V DC applications
- **15 Amp, Double Pole**
15A, 277V AC;
3/4 HP, 125-277V AC
Suitable for 15A, 12V DC applications
- **17 Amp, 3 Pole and 4 Pole**
UL Recognized
17A, 125-277V AC;
1HP, 125V AC;
2HP, 250V AC 1, 2, or 3 phase
Suitable for 17A, 12V DC applications
CSA Certified
17A, 125-250V AC;
1HP, 125V AC;
2HP, 250V AC 1, 2, or 3 phase



6 Amp, Double Pole - Available While Supplies Last

6A, 125V AC; 3A, 250V AC; 1/4HP, 125-250V AC, 50/60 Hz, Suitable for 6A, 12V DC applications

6 Amp, Double Pole	Circuitry			Poles	Cat. No.	Cat. No.	Substitute	Note	Cat. No.	Substitute	Note
	A	B	C		Screw Terminal	Solder Terminal	Screw/Solder		1/4" Q.C. Terminal	1/4" Q.C.	
	ON	---	OFF	DPST	1121-0001	1121-0017	0121-0001	Screw Terminal, 15 Amp	1121-0009	0121-0009	15 Amp
	ON	OFF	ON	DPDT	1121-0002	1121-0018	0121-0002	Screw Terminal, 15 Amp	1121-0010	0121-0010	15 Amp
	ON	---	ON	DPDT	1121-0003	1121-0019	0121-0003	Screw Terminal, 15 Amp	1121-0011	0121-0011	15 Amp
	(ON)	OFF	(ON)	DPDT	1121-0004	1121-0020	0121-0004	Screw Terminal, 15 Amp	1121-0012	0121-0012	15 Amp
	(ON)	---	OFF	DPST	1121-0005	1121-0021	0121-0005	Screw Terminal, 15 Amp	1121-0013	0121-0013	15 Amp
	ON	---	(ON)	DPDT	1121-0006	1121-0022	0121-0006	Screw Terminal, 15 Amp	1121-0014	0121-0014	15 Amp
	ON	OFF	(ON)	DPDT	1121-0007	1121-0023	0121-0007	Screw Terminal, 15 Amp	1121-0015	0121-0015	15 Amp

() Momentary

15 Amp, Double Pole

15A, 277V AC; 3/4HP, 125-277V AC, Suitable for 15A, 12V DC applications

15 Amp, Double Pole	Circuitry			Poles	Cat. No.	
	A	B	C		Screw Terminal	1/4" Q.C. Terminal
	ON	---	OFF	DPST	0121-0001	0121-0009
	ON	OFF	ON	DPDT	0121-0002	0121-0010
	ON	---	ON	DPDT	0121-0003	0121-0011
	(ON)	OFF	(ON)	DPDT	0121-0004	0121-0012
	(ON)	---	OFF	DPST	0121-0005	0121-0013
	ON	---	(ON)	DPDT	0121-0006	0121-0014
	ON	OFF	(ON)	DPDT	0121-0007	0121-0015
	(OFF)	---	ON	DPST	0121-0043	0121-0044

() Momentary

15 Amp, Double Pole - Available While Supplies Last

15A, 277V AC; 3/4HP, 125-277V AC, Suitable for 15A, 12V DC applications

15 Amp, Double Pole - Available While Supplies Last	Circuitry			Poles	Cat. No.	Substitute #1	Note	Substitute #2	Note
	A	B	C		Solder Terminal				
	ON	--	OFF	DPST	0121-0017	0121-0001	Screw Terminal	0121-0009	1/4" Q.C.
	ON	OFF	ON	DPDT	0121-0018	0121-0002	Screw Terminal	0121-0010	1/4" Q.C.
	ON	--	ON	DPDT	0121-0019	0121-0003	Screw Terminal	0121-0011	1/4" Q.C.
	(ON)	OFF	(ON)	DPDT	0121-0020	0121-0004	Screw Terminal	0121-0012	1/4" Q.C.
	(ON)	--	OFF	DPST	0121-0021	0121-0005	Screw Terminal	0121-0013	1/4" Q.C.
	ON	--	(ON)	DPDT	0121-0022	0121-0006	Screw Terminal	0121-0014	1/4" Q.C.
	ON	OFF	(ON)	DPDT	0121-0023	0121-0007	Screw Terminal	0121-0015	1/4" Q.C.
	(OFF)	--	ON	DPST	0121-0045	0121-0043	Screw Terminal	0121-0044	1/4" Q.C.

() Momentary

17 Amp, 3 Pole

UL Recognized, 17A, 125-277V AC; 1HP, 125V AC; 2HP, 250V AC 1, 2, or 3 phase, Suitable for 17A, 12V DC applications, CSA Certified, 17A, 125-250V AC; 1HP, 125V AC; 2HP, 250V AC 1, 2, or 3 phases

17 Amp, 3 Pole	Circuitry			Poles	Cat. No.	
	A	B	C		Screw Terminal	1/4" Q.C. Terminal
	ON	--	OFF	3PST	0140-3020	0140-3000
	(ON)	--	OFF	3PST	0140-3021	0140-3001
	ON	OFF	ON	3PDT	0140-3023	0140-3003
	ON	--	ON	3PDT	0140-3024	0140-3004
	ON	--	(ON)	3PDT	0140-3025	0140-3005
	ON	OFF	(ON)	3PDT	0140-3026	0140-3006
	(ON)	OFF	(ON)	3PDT	0140-3027	0140-3007

() Momentary

17 Amp, 3 Pole - Available While Supplies Last

UL Recognized, 17A, 125-277V AC; 1HP, 125V AC; 2HP, 250V AC 1, 2, or 3 phase, Suitable for 17A, 12V DC applications, CSA Certified, 17A, 125-250V AC; 1HP, 125V AC; 2HP, 250V AC 1, 2, or 3 phases

17 Amp, 3 Pole - Available While Supplies Last	Circuitry			Poles	Cat. No.	Substitute	Cat. No.	Substitute #1	Note	Substitute #2	Note	1/4" Q.C. Terminal	Substitute
	A	B	C		Screw Terminal		Solder Terminal						
	ON	---	OFF	3PST			0140-3010	0140-3020	Screw Terminal	0140-3000	1/4" Q.C.		
	(ON)	---	OFF	3PST			0140-3011	0140-3021	Screw Terminal	0140-3001	1/4" Q.C.		
	ON	---	(OFF)	3PST	0140-3022	No Substitute Available	0140-3012	No Substitute Available			1/4" Q.C.	0140-3002	No Substitute Available
	ON	OFF	ON	3PDT			0140-3013	0140-3023	Screw Terminal	0140-3003	1/4" Q.C.		
	ON	---	ON	3PDT			0140-3014	0140-3024	Screw Terminal	0140-3004	1/4" Q.C.		
	ON	---	(ON)	3PDT			0140-3015	0140-3025	Screw Terminal	0140-3005	1/4" Q.C.		
	ON	OFF	(ON)	3PDT			0140-3016	0140-3026	Screw Terminal	0140-3006	1/4" Q.C.		
	(ON)	OFF	(ON)	3PDT			0140-3017	0140-3027	Screw Terminal	0140-3007	1/4" Q.C.		

() Momentary

17 Amp, 4 Pole

UL Recognized, 17A, 125-277V AC; 1HP, 125V AC; 2HP, 250V AC 1, 2, or 3 phase, Suitable for 17A, 12V DC applications, CSA Certified, 17A, 125-250V AC; 1HP, 125V AC; 2HP, 250V AC 1, 2, or 3 phases

17 Amp, 4 Pole	Circuitry			Poles	Cat. No.	
	A	B	C		Screw Terminal	1/4" Q.C. Terminal
	ON	--	OFF	4PST	0140-4020	0140-4000
	(ON)	--	OFF	4PST	0140-4021	0140-4001
	ON	OFF	ON	4PDT	0140-4023	0140-4003
	ON	--	ON	4PDT	0140-4024	0140-4004
	ON	--	(ON)	4PDT	0140-4025	0140-4005
	ON	OFF	(ON)	4PDT	0140-4026	0140-4006
	(ON)	OFF	(ON)	4PDT	0140-4027	0140-4004

17 Amp, 4 Pole - Available While Supplies Last

UL Recognized, 17A, 125-277V AC; 1HP, 125V AC; 2HP, 250V AC 1, 2, or 3 phase, Suitable for 17A, 12V DC applications, CSA Certified, 17A, 125-250V AC; 1HP, 125V AC; 2HP, 250V AC 1, 2, or 3 phases

17 Amp, 4 Pole - Available While Supplies Last	Circuitry			Poles	Cat. No.	Substitute	Cat. No.	Substitute #1	Note	Substitute #2	Note	1/4" Q.C. Terminal	Substitute
	A	B	C		Screw Terminal		Solder Terminal						
	ON	---	OFF	4PST			0140-4010	0140-4020	Screw Terminal	0140-4000	1/4" Q.C.		
	(ON)	---	OFF	4PST			0140-4011	0140-4021	Screw Terminal	0140-4001	1/4" Q.C.		
	ON	---	(OFF)	4PST	0140-4022	No Substitute Available	0140-4012	No Substitute Available			1/4" Q.C.	0140-4002	No Substitute Available
	ON	OFF	OFF	4PDT			0140-4013	0140-4023	Screw Terminal	0140-4003	1/4" Q.C.		
	ON	---	ON	4PDT			0140-4014	0140-4024	Screw Terminal	0140-4004	1/4" Q.C.		
	ON	---	(ON)	4PDT			0140-4015	0140-4025	Screw Terminal	0140-4005	1/4" Q.C.		
	ON	OFF	(ON)	4PDT			0140-4016	0140-4026	Screw Terminal	0140-4006	1/4" Q.C.		
	(ON)	OFF	(ON)	4PDT			0140-4017	0140-4027	Screw Terminal	0140-4007	1/4" Q.C.		

Dimensions

Switch Series	Bushings	Bats	Case
1121, 0121 Series	15/32" - 32 thread 15/32" long	9/16" long	1 15/64" x 51/64"
0140 Series	15/32" - 32 thread 15/32" long	9/16" long	1 5/16" x 15/32"

Note: Mounting hardware and terminal screws (where applicable) furnished unassembled. Mounting hardware consists of one plated hex nut and knurl nut. Indicating plate is also furnished for maintained ON-OFF circuits.