

 Search This Product Catalog

 Access Network Solutions
 Product Catalog for Access Network Solutions

- 3M™ Dynatel™ Diagnostic Test Equipment
- Cabinets
- Copper Splicing
- Fiber and Copper Closures and Terminals
- Fiber Cable Assemblies
- Fiber Connectors, Splices, Couplings and Cable Assemblies
- Fiber Management Systems
- Locating and Marking Systems
- Quante Products
- Related Products

 Other Tools

- Where to Buy

[Product Catalog for Access Network Solutions](#) > [Related Products](#) > [Static Control](#)

3M™ Metal-In Static Shielding Bag 1910, 10 in. x 12 in., Reclosable (100/Package) [P](#)


[\[click to enlarge\]](#)

3M Id : 98-0798-2205-6

GTIN(UPC/EAN) : 0 00 54007 49266 5

Additional Information

The 3M™ Metal-In Static Shielding Bag 1900/1910 is an economical alternative shielding bag for less demanding applications

where testing and reusing bags are not prime considerations. Aluminum coated on half-mil polyester. This shielding layer is bonded between the layer and a static-dissipative polyethylene inner layer. The 1900/1910 amine-free, non-corrosive and

Learn More . . .
[Packaging Data](#)
[Full Text . . .](#)
Characteristics

Amine Free	Yes
Biodegradable	No
Coating	Aluminum w/Vapor
Color	Silver
Conductive	No
Cushioned	No
Custom Printing	Yes
Disposable	Yes
Dissipative	Yes
Non-Corrosive	Yes
Primary Trademark Name	3M
Shelf Life	12 Month
Static Shielding	Metal In
Thickness	2.9 Milli-inch (Mil)
Volume Conductive	No



© 3M 1995-2006

[Legal Information](#)

[Privacy Policy](#)

[Contact Us](#)

[About 3M](#)

[Search](#)