

Solutions for Electronic Specialty Markets (ESM)

Product Catalog for Electronic Specialty Markets

- 3M Electronic Specialty Markets New Product Releases
- 3M Abrasives
- 3M Adhesives, Cleaners & Compounds
- 3M Breadboards & Test Clips
- 3M Cable & Assemblies
- 3M Copper Interconnects
- 3M Fiber Optics
- 3M Fire Protection
- 3M Heat Shrink
- 3M Identification Systems
- 3M Occupational Health & Safety Products
- 3M Protective Bumpers
- 3M Reclosable Fasteners
- 3M Splicing, Terminating & Ducting
- 3M Static Control
- 3M Tapes
- 3M Terminals, Kits & Tools
- 3M Vacuums & Accessories
- 3M Warehousing & Packaging Supplies
- 3M Wire Connectors

Other Tools

- What's New
- Sales Contacts
- U.S. Distributors

Search This Product Catalog

By Keyword ▼

[Product Catalog for Electronic Specialty Markets](#) [3M Terminals, Kits & Tools](#) [Forks](#)
[Highland Block Fork Terminals - Non-Insulated Butted Seam](#)

3M Highland Block Fork Non Insulated BF18-6C, 22-18 AWG, 100 per bag [Printer-friendly format](#)

This block fork accepts a 6 stud size and case quantities of 500.

GTIN(UPC/EAN) : 0 00 54007 70200 9
 3M Id : 80 - 6105 - 5512 - 2

Additional Information


This block fork has the same strength as the standard fork, but is designed to use in a terminal block because its sides lie flat against the barrier portion of the terminal block.

Learn More . . .

- [Packaging Data](#)
- [Highland Block Forks - Non - Insulated - Product Selection Guide \(PDF 8.1 K\)](#)
- [Highland Terminals BF18 -6 - BF10 - Data Sheet \(PDF 26.9 K\)](#)
- [Terminal Stud Size Chart - Product Selection Guide \(PDF 5.2 K\)](#)

Please Note:

Adobe® Acrobat® Reader is required to view PDF documents.



Characteristics

Agency Approvals	UL and CSA
Barrel Style	Butted
China RoHS - Below MCV	Yes
CSA File Number	LR22190
EPC Can View	Public
EU RoHS Compliant	Yes
Stud Size	6 American Wire Gauge (AWG)
Terminal Style	Block
Terminal Type	Fork
UL File Number	E23438
Wire Gauge Range	18 to 22 American Wire Gauge (AWG)