

Solutions for Electronic Specialty Markets (ESM)

Product Catalog for Electronic Specialty Markets

- 3M Electronic Specialty Markets New Product Releases
- 3M Abrasives
- 3M Adhesives, Cleaners & Compounds
- 3M Breadboards & Test Clips
- 3M Cable & Assemblies
- 3M Copper Interconnects
- 3M Fiber Optics
- 3M Fire Protection
- 3M Heat Shrink
- 3M Identification Systems
- 3M Occupational Health & Safety Products
- 3M Protective Bumpers
- 3M Reclosable Fasteners
- 3M Splicing, Terminating & Ducting
- 3M Static Control
- 3M Tapes
- 3M Terminals, Kits & Tools**
- 3M Vacuums & Accessories
- 3M Warehousing & Packaging Supplies
- 3M Wire Connectors

Other Tools


- What's New
- Sales Contacts
- U.S. Distributors

Search This Product Catalog

By Keyword

[Product Catalog for Electronic Specialty Markets](#) [3M Terminals, Kits & Tools](#) [High Temperature](#) [Scotchlok High Temperature Female Disconnects](#) - [Butted Seam](#)

3M Scotchlok High Temperature Butted Seam Female Disconnect MU14 -250DFHTX, 16-14 AWG [Printer-friendly format](#)



This terminal has a wire range of 16 - 14 AWG and case quantities of 500 per case.

[\[click to enlarge\]](#)

GTIN(UPC/EAN) : 0 00 54007 49632 8
3M Id : 80 - 6105 - 9367 - 7


Additional Information

The disconnects are attached to mating part by tongue of female part slipping over male tab. The use of dents and rolled edges on female part provides excellent holding force while allowing easy and quick disconnect.

Learn More . . .

- [Packaging Data](#)
- [Scotchlok Terminals MU14 - 187DFHT/MU14 - 250DFHT - Data Sheet \(PDF 15.8 K\)](#)

Please Note:
Adobe® Acrobat® Reader is required to view PDF documents.



Characteristics

Barrel Style	Butted
China RoHS - Below MCV	Yes
EPC Can View	Public
EU RoHS Compliant	Yes
Fastener Orientation	Female
Insulated	No
Pad Width	0.250 Inch
Terminal Style	High Temp
Terminal Type	Disconnect
Wire Gauge Range	14 to 16 American Wire Gauge (AWG)