



## Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)[United States](#) > [All 3M Products](#) > [Market Segments](#) > [Electronics, Electrical, and Communications](#) > [Electrical Products](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Heat Shrink](#) > [Single \(Thin\) Wall Tubing](#) > [3M™ Heat Shrink FP-301](#) > [3M™ Heat Shrink Thin-Wall Tubing FP-301-3/4-Black-200`](#): 200 ft spool length, 600 ft per case[Find An Account Rep](#)[Where To Buy \(Find A Distributor\)](#)[Contact Us](#)

## 3M™ Heat Shrink Thin-Wall Tubing FP-301-3/4-Black-200`: 200 ft spool length, 600 ft per case

3M ID 80610219703 UPC# 00054007085027 3M Product Number FP301-3/4-200'-Black-Spool

[Print](#) [Share](#)

3M™ Heat Shrink Tubing FP-301 offers an outstanding balance of electrical, physical and chemical properties for a wide variety of industrial and military applications. This tubing comes in a bulk spool.

[Buy at Shop3M.com](#)**Need Help?**

**Questions?** We can help  
[Contact Us](#)

**Overview****Documentation****Specifications**

<b>Agency Approvals</b>	UL Recognized, CSA Certified, ABS, and AMS 3636 & 3637
<b>China RoHS - Below MCV</b>	Yes
<b>Color</b>	Black
<b>Dielectric Strength</b>	900 Volt
<b>Elongation</b>	400 Percent
<b>EU RoHS Compliant</b>	Yes
<b>Expanded Inner Diameter</b>	3/4 Inch
<b>Flammability Rating</b>	UL 224 All Tubing Flame Test
<b>Length</b>	200 Linear Foot
<b>Material</b>	Flexible Polyolefin
<b>Mil Spec</b>	AMS-DTL-23053/5, Class 1
<b>Non-Corrosive</b>	Yes
<b>Operating Temperature Range (Celsius)</b>	-55 Degrees C to +135 Degrees C
<b>Recovered Inner Diameter</b>	3/8 Inch
<b>Shrink Ratio</b>	2:1
<b>Tensile Strength</b>	2400 Pound-Force Per Square Inch
<b>Tubing Type</b>	Single-Wall Polyolefin Flexible
<b>UL File Number</b>	E-39100

