All 3M Products Innovation About 3M

United States [Change]

A Electrical Commercial and Industrial

Products

Documentation & Literature

News & Tradeshows

Support

United States > All 3M Products > Market Segments > Electronics, Electrical, and Communications > Electrical Products > Electrical Commercial and Industrial > Products > Electrical Commercial & Industrial Products Catalog > Terminals, Kits and Tools > Terminals > 3M™ Highland™ Ring Tongues > 3M™ Highland™ Vinyl Insulated Ring Terminal RV18-8Q, AWG 22-18, 25/bag

Find An Account Rep

D w

Where To Buy (Find A Distributor)






3M™ Highland™ Vinyl Insulated Ring Terminal RV18-8Q, AWG 22-18, 25/bag

3M ID 80611603079 UPC# 00051128600467 3M Product Number RV18-8Q

roduct Number RV18-8Q

Semoto

Print Share



This terminal accepts a wire range of 22-18, a stud size of 8 and has a case quantity of 10 bags.

Need Help?

Questions? We can help

Contact Us

Like Sign Up to see what your friends like.

Overview Documentation

Agency Approvals	UL and CSA
Barrel Inside Diameter	0.07 Inch
Barrel Length	0,25 Inch
Barrel Style	Butted
Brand	Highland
China RoHS - Below MCV	Yes
Clearance (C)	0,33 Inch
Conductor Sizes	22 - 18 AWG
CSA File Number	LR22190
Dimension E	0.78 Inch
EU RoHS Compliant	Yes
Insulation Material	Vinyl
Length (L)	0.93 Inch
Maximum Insulation Outer Diameter	0.145 Inch
Packaging	25 per bag
Stud Size	8
Terminal Style	Standard
Terminal Type	Ring
Thickness	0.03 Inch
UL File Number	E23438
Width (W)	0.31 Inch

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

3M: News | Careers | Investor Relations | MSDS Search | Transport Information Search | A-Z Product Index | Contact 3M

Legal Information | Privacy Policy

© 3M 2014, All Rights Reserved.

