



Electrical Commercial and Industrial

- Products
- Documentation & Literature
- News & Tradeshows
- Support

United States > All 3M Products > Energy > Electrical Commercial and Industrial > Products > Product Catalog

[Find An Account Rep](#)

[Where To Buy \(Find A Distributor\)](#)

[Contact Us](#)

Electrical Commercial & Industrial Products Catalog > Terminals, Kits and Tools > Terminals > 3M™ Scotchlok™ Pin Nylon Insulated, 50/bottle, MNG10-55PX-A

3M™ Scotchlok™ Pin Nylon Insulated, 50/bottle, MNG10-55PX-A

3M ID: 80611465107 UPC#: 00051128588642 Part Number: MNG10-55PX-A

Pin Nylon Insulated, 50/bottle, MNG10-55PX-A



Need Help?

Questions? We can help
[Contact Us](#)

Overview

Specifications

Barrel Style	Insulation Grip
Brand	Scotchlok
Conductor Sizes	12 - 10 AWG
Insulation Material	Nylon
Length	1.06 Inch
Maximum Insulation Outer Diameter	0.270 Inch
Packaging	50 per bottle
RoHS 2011/65/EU Compliant	Yes
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption. *Important RoHS information
Terminal Type	Pin
Trademark	Scotchlok

