

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0398600109**
Status: **Obsolete**
Description: 5.08mm (.200") Pitch Beau™ Eurostyle™ Pluggable PCB Terminal Block, 180° Wire Entry, 9 Circuits
Replacement Part Number: 39530-0009

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA LR25562
 UL E48521

General

Product Family Terminal Blocks
 Series 39860
 Application Wire-to-Board
 Comments Other housing colors available
 Component Type Plug
 Product Name Eurostyle™ Pluggable
 Replacement Part Number 39530-0009
 Type Euro Block

Physical

Circuits (Loaded) 9
 Color - Resin Black
 Entry Angle 180° Angle
 Flammability 94V-0
 Lock to Mating Part None
 Material - Metal Phosphor Bronze
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Nylon
 Number of Rows 1
 Orientation Horizontal
 PCB Retention N/A
 Panel Mount No
 Pitch - Mating Interface 5.08mm (.200")
 Pitch - Termination Interface 5.08mm (.200")
 Plating min - Mating 5.080µm (200µ")
 Plating min - Termination 5.080µm (200µ")
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating 110°C
 Wire Size AWG 12, 14, 16, 18, 20, 22, 24, 26
 Wire Size mm² 0.20 - 2.50

Electrical

Current - Maximum per Contact 15A
 Voltage - Maximum 300V

Material Info

Old Part Number 860509

Reference - Drawing Numbers

Sales Drawing SD-39860-001

EU RoHS **China RoHS**

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

39860Series

Mates With

39860 Headers

This document was generated on 05/10/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION