

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0847320002](#)
Status: **Active**
Overview: [Sealed Industrial USB Solutions](#)
Description: Sealed Industrial USB Type A Plug-to-Sealed Industrial USB Type B Plug Double Ended Cord Set, 1.50m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	84732
Assembly Configuration	Dual Ended Connectors
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	USB Type A-to-Pigtail
Overview	Sealed Industrial USB Solutions
Product Name	Industrial USB
UPC	822348749331

Physical

Cable Length	1.50m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Plug
Lock to Mating Part	None
Material - Resin	PVC
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Single Ended	No
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Insulation Diameter	3.5mm (.14")
Wire Size AWG	N/A
Wire/Cable Type	USB

Electrical

Current - Maximum per Contact	1.0A
Impedance	Non-constant
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-84732-001
---------------	--------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[84732](#) Series

Mates With

[84729](#) Sealed Industrial USB 2.0 Type A Panel Mount Receptacle to Sealed Industrial USB 2.0 Type A Plug Cordset. [84730-0001](#) Sealed Industrial USB 2.0 Type B Panel Mount PCB Receptacle