

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0745460807](#)
Status: **Active**
Overview: [iPass™ Connector System](#)
Description: [iPass™ PCIe x8 Cable Assembly, 24 AWG, 7.0m Length](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR64395
 UL E72548

General

Product Family Cable Assemblies
 Series [74546](#)
 Assembly Configuration Dual Ended Connectors
 Connector to Connector PCI Express*-to-PCI Express*
 Overview [iPass™ Connector System](#)
 Product Name iPass™, PCI Express*
 UPC 822350025881

Physical

Cable Length 7.0m
 Circuits (Loaded) 68
 Gender Male-Male
 Lock to Mating Part Yes
 Material - Metal Zinc Alloy
 Net Weight 4525.000/g
 Packaging Type Bag
 Pitch - Mating Interface 0.80mm
 Single Ended No
 Waterproof / Dustproof No
 Wire Insulation Diameter N/A
 Wire Size AWG 24
 Wire/Cable Type Round

Electrical

Current - Maximum per Contact 1.0A
 Shielded Yes
 Voltage - Maximum 30V DC

Material Info

Reference - Drawing Numbers

Sales Drawing SD-74546-800

*PCI Express is a registered trademark of PCI-SIG



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
 ED/01/2017 (12
 January 2017)
 2,4-Di-tert-butyl-6-(5-
 chlorobenzotriazol-2-
 yl)p

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[74546 Series](#)

Mates With

[75586 iPass™ Receptacle](#)

Use With

[74540 PCIe Guide Frame](#)