

Home:

Part Number: 63445-1521
ANVIL


Series image - Reference only

Status: Active

Series: [T9999](#)

Category: Molex Parts

Go to [Part Detail](#)

[CHECK DISTRIBUTOR INVENTORY](#)
[Add to My Parts](#)
Specifications & Other Documents:

Documents not available online

Note - Please disable browser pop-up blockers to view documents on [www.molex.com](#)

Questions on Product Environmental Compliance? Email productcompliance@molex.com

[EU RoHS](#) : ELV and RoHS Compliant

[China RoHS](#) :

[REACH SVHC](#) : Not Reviewed

[Low-Halogen Status](#) : Not Reviewed

[Product Compliance Statement](#)
Application Tooling
[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
[Check our list of old tooling that used to be available for this part](#)
Part Detail
[SHOW ALL](#)
General

Status	Active
Category	Molex Parts
Series	T9999
UPC	756054907399

Material Info
Molex Connectors

- Wire-to-Board
- Board-to-Board
- Wire-to-Wire
- Input/Output (IO)
- FFC/FPC
- Sockets

Other Products

- Fiber Optic Products
- Antennas
- Industrial Automation
- Membrane Switches
- Copper Flex
- PCB Assemblies
- Woodhead Electrical
- Solid State Lighting

Resources

- Contact Us
- Catalog
- Cross-Reference
- Industries
- Literature
- Product Name

Company Info

- About Us
- Careers
- ecocare
- Investors
- Press Room
- Shows & Events
- Supplier Portal

Other Info

- Feedback
- Help
- Legal Disclaimer
- View Mobile Site
- Privacy Policy
- Sitemap

Stay Connected with Molex: