## Honeywell


See full Datasheet below ...







masterelectronics.com & onlinecomponents.com are **authorized** e-commerce distributors of electronic components.



AND I	sтн	E PROF	PERTY OF	MICRO	SWITCH.	A DIVISION OF	
PIED	OR U	SED WI	THOUT I	HE APPR	OVAL OF	MICRO SWITCH	

οριε	DOR	USED	WIT	ноит	ΙH	E AP	PROV	AL OF	• MICR	O SW	ИТСН		
	MILITARY RATING (AMPS)												
ΤE	М	ILIT	AR	Y	DC	RES I VOL		VE LOA	AD /OLTS	L A M L O A		INDU(	
Y		T A N C J M B E		D	28	125		125	250	28 VDC	125 VAC	28 VDC	125 VAC
	MSZ	2452	23-										
	MSZ	2452 2452	23-	23	20			15	6	5	3	15	10
		2 <u>452</u> 2452				(REF	FER I	to li I	91 FO	R UL	RAT	ING)	
	MSZ	2452	23-	29									
	MSa	2 <u>452</u> 2452	23-	3   3 0	15	. 75	. 5	15	6	4	2	10	7
Ν		2452 2452		27 26	10	( RE			92 FC			ING)	
Ν	MSZ	2452 2452	3 -	32									
		2432		20	Т		ł				$\sim$		
							I		-	Ľ	✐	-	
							-		·		Ľ	<b>–</b>	
						_		► (.0			$\wedge$	Lø	5.60
							l	_ OC K	WASH	EK 2	/3 \		
						. (	)5 🗕				-	110 ↓	
												- 92	
	$ \qquad \qquad$											_	
					.040 - Ø.72								
					LOCKING RING 3								
									7		′32- READ	32 N	١S
								R	ú	A			
								<u> </u>	Ţ	Ĺ	プ	•	
										.5			
						.01	8 -				$\wedge$		
					L			2 X F	HEX N	UT ,	/3\		
							ſ		THIRD A		_	-	
	SCALE FULL												
							ļ		DO NOT	SCAL			
									SS OTH TOU PLACE	ERAN	ICES /	A R E	
50	277	VAC			<b>SP</b>	(	6	TWO I	PLACE		(.00)	<u>+</u> .	0   5
YAC	:  /	2 HP	- <u>2 5</u>	0,	27	<b>V</b> 7	N AC	THRE	E PLAC Es	СE	(.000	)) ±. ±	005
'L"	С	ODE L	- 192	2	Z				IT .	07 l	_BS .		ОХ
				_									