




2TL1-10B

(Home : Products : Switches : MICRO SWITCH™ Toggle Switches : TL)



TL Series Toggle Switch, 2 pole, 3 position, Screw terminal, Locking Lever, Military Part Number MS27408-4B

Actual product appearance may vary.

Sales & Service

Distributor Inventory

Overview

Specs

Documentation

Description

MICRO SWITCH™ TL Series toggle switches have high strength, temperature resistant, non-tracking case material and silver cadmium oxide contacts. Pull-to-Unlock toggle levers prevent accidental operation; the lever must be pulled approx. 2,3 mm (0.09 inches) to change positions.

Features

- Qualified to MIL-DTL-3950
- Environment-proof sealing
- 1,2, and 4 pole circuitry
- Standard and pull-to-unlock levers
- 2 and 3 position, maintained and momentary toggle action
- Temperature range: -85DF to +160DF
- Completely sealed switching chamber
- Step-design case provides added space between terminals to help prevent shorting
- UL recognized, CSA certified
- CE approved

Potential Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

Product Search

Product Type:

New Products Only

Industry:

Entire Product Catalog

Search Term:

Search

Distributor Inventory

Input part number for stock availability

Narrow Your Search

Modify Your Search

Products

Select Option

Technology

Select Option

Industries Served

Select Option

My Links

- [eCOM Login](#)
- [Request Access to eCOM](#)
- [Rep/AD Portal Login](#)
- [Rep/AD Portal Access Request](#)
- [Sample Request](#)
- [Digital U - HVM Learning Hub Login](#)
- [Limitless Microsite](#)
- [Supplier Microsite](#)

Literature and Media

- [Data Sheets](#)
- [Videos](#)
- [Literature](#)
- [Literature Request](#)
- [White Papers](#)
- [Application Notes](#)
- [Application Demos](#)
- [CAD Renderings](#)

Contacts

- [Customer Service](#)
- [Technical Support](#)
- [Global Sales & Service](#)