



Deutsche Version

[Home](#)

[About Us](#)

**Products**

**Audio**

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

PRODUCTS ONLY

© Neutrik® AG  
All rights reserved  
[Legal Notices](#)



Audio

## Circular Adapters

[back](#)

### NA3F5F

Product	
Connector Type	Adapter
Electrical	
Contact resistance	≤ 3 mΩ
Dielectric strength	1,5 kVdc
Insulation resistance	> 2 GΩ
Rated current per contact	7,5 A
Mechanical	
Insertion force	< 20 N
Withdrawal force	< 20 N
Lifetime	> 1000 mating cycles
Locking device	Latch lock
Material	
Contact plating	2 μm Ag
Contacts	Bronze (CuSn6) (3 pole female)
Contacts	Brass (CuZn39Pb3) (5 pole female)
Insert	Polyamide (PA 6.6 30 % GR)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Environmental	
Temperature range	-30 °C to +80 °C