



Deutsche Version

[Home](#)

[About Us](#)

Products

Audio

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

PRODUCTS ONLY

Search

© Neutrik® AG
All rights reserved
[Legal Notices](#)



Audio

Phono (RCA)

[back](#)

NYS352B

Product

Connector Type	Plug
Gender	male

Electrical

Contact resistance	< 10 mΩ
Dielectric strength	0,5 kVdc
Rated current per contact	depends on mated connector A

Mechanical

Cable O.D.	≤ 7 mm
Lifetime	5000 mating cycles
Wire size	24 AWG

Material

Contact plating	2 μm Ni
Contacts	Brass (CuZn39Pb3)
Insert	PC
Shell	Brass (CuZn39Pb3) Black
Strain relief	CRIMP type snce plated

Environmental

Solderability	Complies with IEC 68-2-20
Temperature range	-20 °C to +70 °C