



Twisted Pair & Flat
Phone Cable

Fiber Optic Cable

Coaxial Cable

Electrical and Industrial

Bench/Other Hand Tools

What's New

Coaxial Cable > Crimpers > 1300 Series

We also suggest

RG6 & RG58 1300 Series Crimper

Part number: 1348 Technical

Part numbers

Tool & Die: 1348

Die only: 2076

Description

Crimps BNC/TNC coaxial connectors.

Type

RG6, RG58

Crimp size

.320/.210/.185" HEX

Connector style

AIM, Cambridge, Kings, Amphenol, GEM



PowerPlay® PT-
525



SealTite® Pro
Compression
Crimper - RCA,
BNC, Cable TV F
(RG59/6/6 Quad)



All-in-One Data &
Phone Tool
(WE/SS-style)



Combo UTP/Coax
SureStrip®
Cutter/Stripper



BroadcastReady™
Kit