

Electrical and Industrial > Crimpers > **1600 Series**

We also suggest



1600 Series Professional Open-Barrel D-Sub Pin Crimper - 1646

Part number: 1646

Description

Crimps 28-20 AWG (.08-.5 mm²) open barrel D-sub contact pins. Fixed die system.

Type

28-20 AWG (.08-.5 mm²) stranded wire

Crimp size

28-24/22-20 F-Type

Connector style

Standard D-sub pins only



1600 Series Professional Insulated Terminal & Lug Crimper - 1605



Professional 20-12 AWG Wire Ferrule Crimper - 1648



1300 Series Wire Ferrule Crimper - 1360

[Home](#) | [BuyNOW!](#) | [Connector Cross-Reference](#) | [Distributors](#) | [Contact us](#)**PowerPlay**
Tool give-away