

## Protective covers - HC-D 15-SD-FL/FS - 1660164


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON protective cover, type D15, for supporting base element with single locking latch, with retaining cord, IP54, PA



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 021900
Weight per Piece (excluding packing)	15.24 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Diameter of retaining cord eyelet	30 mm
-----------------------------------	-------

#### Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 100 °C

#### General

Type	D15
	For supporting base element with single locking latch
Seal material	NBR
Flammability rating according to UL 94	HB
Seal present	yes
Connection	Plastic protective cover for short-term protection

# Protective covers - HC-D 15-SD-FL/FS - 1660164

## Technical data

### Standards and Regulations

Flammability rating according to UL 94	HB
--	----

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC002314

### UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

## Protective covers - HC-D 15-SD-FL/FS - 1660164

### Approvals

Approvals submitted


---

### Approval details

EAC
-----

### Drawings

Dimensional drawing



Dimensional drawing